

Mallia™ Senses

fan controls, cooker control units and panic buttons



2 810 75DS



2 810 49DS

Dimensions: 86 x 86 mm (1-gang) / 146 x 86 mm (2-gang)
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film

Pack	Cat.Nos
1	2 810 82BA
1	2 810 82BB
1	2 810 82CH
1	2 810 82DB
1	2 810 82DS
1	2 810 82MB
1	2 810 82MW

Fan speed controls

Conform to BS EN 60669-2-1

5-speed fan controls

100 W for fan with overall diameter 48"



- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

5	2 810 75BA
5	2 810 75BB
5	2 810 75CH
5	2 810 75DB
5	2 810 75DS
5	2 810 75MB
5	2 810 75MW

Cooker control units 45 A - 250 VA

Conform to BS 4177

45 A DP switch + 13 A switched socket outlet with red indicator



- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

1	2 810 49BA
1	2 810 49BB
1	2 810 49CH
1	2 810 49DB
1	2 810 49DS
1	2 810 49MB
5	2 810 49MW

Panic buttons

1 A resistive - 250 VA



- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

Mallia™ Senses

telephone and data sockets



2 811 60MW



2 811 66DS

Dimensions: 86 x 86 mm
Compact mechanism for greater wiring space
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film

Pack	Cat.Nos
5	2 811 60BA
5	2 811 60BB
5	2 811 60CH
5	2 811 60DB
5	2 811 60DS
5	2 811 60MB
5	2 811 60MW

Telephone sockets

RJ 11 sockets - 4 contacts

1/4 turn, tool-less connector



- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

5	2 811 63BA
5	2 811 63BB
5	2 811 63CH
5	2 811 63DB
5	2 811 63DS
5	2 811 63MB
5	2 811 63MW

Double RJ 11 sockets - 4 contacts

1/4 turn, tool-less connector



- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

5	2 811 69BA
5	2 811 69BB
5	2 811 69CH
5	2 811 69DB
5	2 811 69DS
5	2 811 69MB
5	2 811 69MW

BS secondary telephone sockets



- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White

5	2 811 66BA
5	2 811 66BB
5	2 811 66CH
5	2 811 66DB
5	2 811 66DS
5	2 811 66MB
5	2 811 66MW

Telephone and data sockets

RJ 11 + RJ 45 sockets Cat. 6 UTP



- Brushed Aluminium
- Brushed Black
- Champagne
- Dark Bronze
- Dark Silver
- Matt Black
- Matt White