

Arteor™

RJ 45 sockets (continued)



5 723 15

Support frame and plate selection charts **p. 594-603**

Can be integrated in any support
Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594-603)
Equipped with connectors with quick toolless connection
Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
T568A and B marking with colour codes
Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

Pack	Cat.Nos	Cat. 5e sockets
10	5 723 03	UTP - 1 module <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 728 03	
10	5 700 58	
10	5 710 58	
10	5 723 15	UTP - 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 728 15	
10	5 728 99	
10	5 728 98	
10	5 723 04	FTP - 1 module <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 728 04	
10	5 729 08	
10	5 729 07	

Arteor™

rear pluggable data sockets



5 723 31

5 728 32

5 723 36

5 728 35

Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594-603)

Pack	Cat.Nos	Rear pluggable RJ 45 sockets
		Certified as conforming to standards ISO 11801 ed. 2.0, EN 50173-1 and EIA/TIA 568 Contacts marked with 568 A and B dual colour code and numbers Connectors with self-stripping terminals Possibility of re-wiring in the event of error Multidirectional cable entry For use with area distribution boxes connection to boxes via RJ 45-RJ 45 dedicated cords Used to create cat. 6 and cat. 5e links in accordance with standards 2 modules
		Cat. 6 - UTP <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 723 31	Cat. 6 - FTP <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 728 31	
10	5 729 10	
10	5 729 09	
10	5 723 30	Cat. 5e - UTP <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 728 30	
10	5 729 18	
10	5 729 17	
10	5 723 32	Cat. 5e - FTP <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 728 32	
10	5 729 20	
10	5 729 19	