

# Mallia™ Senses

## British standard socket outlets



2 811 11BA



2 811 15CH



2 811 17MB

Dimensions: 86 x 86 mm (1-gang) / 146 x 86 mm (2-gang)  
 Supplied with 2 screws M 3.5 for BS boxes  
 Supplied as complete product with protective film  
 All sockets integrate child protection

Pack	Cat.Nos	<b>British standard single pole socket outlets 13 A - 250 V~</b>	
		Conform to BS 1363-2	
		<b>1-gang - unswitched</b>	
5	2 811 10BA		● Brushed Aluminium
5	2 811 10BB		● Brushed Black
5	2 811 10CH		● Champagne
5	2 811 10DB		● Dark Bronze
5	2 811 10DS		● Dark Silver
5	2 811 10MB		● Matt Black
10	2 811 10MW		○ Matt White
		<b>2-gang - unswitched</b>	
5	2 811 12BA		● Brushed Aluminium
5	2 811 12BB		● Brushed Black
5	2 811 12CH		● Champagne
5	2 811 12DB		● Dark Bronze
5	2 811 12DS		● Dark Silver
5	2 811 12MB		● Matt Black
5	2 811 12MW		○ Matt White
		<b>1-gang - switched</b>	
5	2 811 11BA		● Brushed Aluminium
5	2 811 11BB		● Brushed Black
5	2 811 11CH		● Champagne
5	2 811 11DB		● Dark Bronze
5	2 811 11DS		● Dark Silver
5	2 811 11MB		● Matt Black
10	2 811 11MW		○ Matt White
		<b>1-gang - switched with red LED power indicator</b>	
5	2 811 14BA		● Brushed Aluminium
5	2 811 14BB		● Brushed Black
5	2 811 14CH		● Champagne
5	2 811 14DB		● Dark Bronze
5	2 811 14DS		● Dark Silver
5	2 811 14MB		● Matt Black
10	2 811 14MW		○ Matt White
		<b>2-gang - switched</b>	
5	2 811 13BA		● Brushed Aluminium
5	2 811 13BB		● Brushed Black
5	2 811 13CH		● Champagne
5	2 811 13DB		● Dark Bronze
5	2 811 13DS		● Dark Silver
5	2 811 13MB		● Matt Black
5	2 811 13MW		○ Matt White
		<b>2-gang - switched with red LED power indicator</b>	
5	2 811 15BA		● Brushed Aluminium
5	2 811 15BB		● Brushed Black
5	2 811 15CH		● Champagne
5	2 811 15DB		● Dark Bronze
5	2 811 15DS		● Dark Silver
5	2 811 15MB		● Matt Black
5	2 811 15MW		○ Matt White

Pack	Cat.Nos	<b>British standard double pole socket outlets 13 A - 250 V~</b>	
		Conform to BS 1363-2	
		<b>1-gang - switched</b>	
5	2 811 16BA		● Brushed Aluminium
5	2 811 16BB		● Brushed Black
5	2 811 16CH		● Champagne
5	2 811 16DB		● Dark Bronze
5	2 811 16DS		● Dark Silver
5	2 811 16MB		● Matt Black
10	2 811 16MW		○ Matt White
		<b>1-gang - switched with red LED power indicator</b>	
5	2 811 18BA		● Brushed Aluminium
5	2 811 18BB		● Brushed Black
5	2 811 18CH		● Champagne
5	2 811 18DB		● Dark Bronze
5	2 811 18DS		● Dark Silver
5	2 811 18MB		● Matt Black
10	2 811 18MW		○ Matt White
		<b>2-gang - switched</b>	
5	2 811 17BA		● Brushed Aluminium
5	2 811 17BB		● Brushed Black
5	2 811 17CH		● Champagne
5	2 811 17DB		● Dark Bronze
5	2 811 17DS		● Dark Silver
5	2 811 17MB		● Matt Black
5	2 811 17MW		○ Matt White
		<b>2-gang - switched with red LED power indicator</b>	
5	2 811 19BA		● Brushed Aluminium
5	2 811 19BB		● Brushed Black
5	2 811 19CH		● Champagne
5	2 811 19DB		● Dark Bronze
5	2 811 19DS		● Dark Silver
5	2 811 19MB		● Matt Black
5	2 811 19MW		○ Matt White