

Hotel equipment

lighting, electric roller blinds, curtain control - square version



Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594-603)

| Pack | Cat.Nos | Lighting control |
|------|----------|---|
| | | Master switch - 2 modules 2-way double pole 20 AX - 250 V~ for general control: all ON / all OFF |
| 10 | 5 732 84 | ○ White |
| 10 | 5 737 84 | ● Magnesium |
| 10 | 5 737 89 | ● Champagne |
| 10 | 5 737 88 | ● Soft Alu |
| | | Master push-button - 2 modules 2-way 6 A - 250 V~ for general control: all ON/ all OFF |
| 10 | 5 732 86 | ○ White |
| 10 | 5 737 86 | ● Magnesium |
| 10 | 5 737 99 | ● Champagne |
| 10 | 5 737 98 | ● Soft Alu |
| | | Switch for bed lights - 2 x 1 module 2 x 2-way switch - 10 AX - 250 V~ |
| 10 | 5 732 94 | ○ White |
| 5 | 5 737 94 | ● Magnesium |
| 5 | 5 737 63 | ● Champagne |
| 5 | 5 737 62 | ● Soft Alu |
| | | Push-button for bed lights - 2 x 1 module 2 x 2-way push-button - 6 A - 250 V~ |
| 10 | 5 732 96 | ○ White |
| 5 | 5 737 96 | ● Magnesium |
| | | Electric roller blinds control - 250 VA |
| | | Double switch 10 A - 2 modules For direct control of a motor (mechanism with fixed positions) |
| 10 | 5 732 22 | ○ White |
| 10 | 5 737 22 | ● Magnesium |
| 10 | 5 737 76 | ● Champagne |
| 10 | 5 737 75 | ● Soft Alu |
| | | Double push-button 10 A - 2 modules For control via automatic box (N/O mechanism) |
| 10 | 5 732 24 | ○ White |
| 10 | 5 737 24 | ● Magnesium |
| | | Curtain control - 250 VA |
| | | Double switch 10 A - 2 modules For direct control of a motor (mechanism with fixed positions) |
| 10 | 5 732 34 | ○ White |
| 10 | 5 737 34 | ● Magnesium |
| | | Double push-button 10 A - 2 modules For control via automatic box (N/O mechanism) |
| 10 | 5 732 36 | ○ White |
| 10 | 5 737 36 | ● Magnesium |

Hotel equipment

lighting, electric roller blinds, curtain control - round version



Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594-603)

| Pack | Cat.Nos | Lighting control |
|------|----------|---|
| | | Master switch - 2 modules 2-way double pole 20 AX - 250 V~ for general control: all ON / all OFF |
| 10 | 5 732 85 | ○ White |
| 10 | 5 737 85 | ● Magnesium |
| | | Master push-button - 2 modules 2-way 6 A - 250 V~ for general control: all ON/ all OFF |
| 10 | 5 732 87 | ○ White |
| 10 | 5 737 87 | ● Magnesium |
| | | Switch for bed lights - 2 x 1 module 2 x 2-way switch - 10 AX - 250 V~ |
| 5 | 5 732 95 | ○ White |
| 5 | 5 737 95 | ● Magnesium |
| | | Push-button for bed lights - 2 x 1 module 2 x 2-way push-button - 6 A - 250 V~ |
| 5 | 5 732 97 | ○ White |
| 5 | 5 737 97 | ● Magnesium |
| | | Electric roller blinds control - 250 VA |
| | | Double switch 10 A - 2 modules For direct control of a motor (mechanism with fixed positions) |
| 10 | 5 732 23 | ○ White |
| 10 | 5 737 23 | ● Magnesium |
| | | Double push-button 10 A - 2 modules For control via automatic box (N/O mechanism) |
| 10 | 5 732 25 | ○ White |
| 10 | 5 737 25 | ● Magnesium |
| | | Curtain control - 250 VA |
| | | Double switch 10 A - 2 modules For direct control of a motor (mechanism with fixed positions) |
| 10 | 5 732 35 | ○ White |
| 10 | 5 737 35 | ● Magnesium |
| | | Double push-button 10 A - 2 modules For control via automatic box (N/O mechanism) |
| 10 | 5 732 37 | ○ White |
| 10 | 5 737 37 | ● Magnesium |

