

**Living Now**

**USB data socket, audio and video sockets**



BT-K4284P

BT-KM4294

BT-KW4269R

Cover plates selection chart **p. 763-764**  
Plates selection chart **p. 778**

To be equipped with a support frame, a cover plate and a plate

Pack	Cat.Nos	USB data socket - for data transfer
1	BT-K4285P	For connecting USB devices (scanner-printer, external hard disk) Preterminated - USB Type-A Equipped with a 15 cm cord 1 module 
1	BT-K4284P	<b>HDMI Type-A socket</b> Used to transmit high-definition digital audio/video streams between a source (computer, Blu-ray player...) and a compatible receiver (TV, videoprojector...) Maximum distance between 2 sockets: 10 m Preterminated HDMI 2.0 1 module Equipped with cord (length 15 cm) and 2 female connectors 1 module 
1 1 1	BT-KW4294 BT-KG4294 BT-KM4294	<b>Loudspeaker socket</b> 1 module To be equipped with a 1-module cover plate (or a 2-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949, p. 776) Terminal 4 mm <sup>2</sup>  ○ White ● Black ● Sand
1 1 1	BT-KW4269R BT-KG4269R BT-KM4269R	<b>Female 2 RCA socket</b> Provides the stereo audio link for any peripheral device such as a DVD drive, camera, video recorder 1 module To be equipped with a 1-module cover plate (or a 2-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949, p. 776)  ○ White ● Black ● Sand

**Living Now**

**hotel functions**



BT-K4549

BT-K4373

BT-KW4362

Cover plates selection chart **p. 765**  
Plates selection chart **p. 778**

To be equipped with a support frame, a cover plate and a plate

Pack	Cat.Nos	Key card switches
1 1	BT-K4549 BT-K4548	For energizing a circuit by inserting a key fob Time-delay of approx. 30 sec. after card removal 2 modules Can be equipped with a 3-module cover plate by associating the mechanism with 2 half-modules Cat.No BT-K4949 (p. 776) For ISO badge or card For RFID badge 
1	BT-K4373	<b>Hotel bedroom call indicators</b> 1 module <b>Indicator for corridor</b> To be installed in the corridor, outside the room Supplied with green/red indicator Cat.No BT-K4743V230RG 
1 1	BT-K4027H BT-K4027V127H	<b>Internal control unit</b> To be installed inside the room Enable the resident to inform hotel staff of the room status Two settings are possible: - Do not disturb - Please clean the room  250 V~ power supply 127 V~ power supply
1 1 1	BT-KW4362 BT-KG4362 BT-KM4362	<b>Reading light</b> Fitted with maintenance-free LEDs LED colours: 3000 K (neutral white) 230 V power supply - energy Class A Screw terminals For installation in the bedhead Offers directional lighting (on/off and dimming) Equipped with a flexible cable so the head can swivel. Built-in dimmer Consumption: 3.3 W Luminous flux 110 lumen (equivalent to 15 W incandescent) Service life 40000 hours 1 module For installation in flush-mounting box  ○ White ● Black ● Sand
1 1 1	BT-KW4177 BT-KG4177 BT-KM4177	<b>Shaver socket</b> 3 modules To be mounted on support frame Cat.No BT-K4703 and flush-mounting box Cat.No BT-PB503N Requires a 3-module plate  ○ White ● Black ● Sand