

Mallia™ Senses

television sockets (continued)



Mallia™ Senses

audio and video sockets






2 811 51CH



2 811 52DS

Dimensions: 86 x 86 mm
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film

Pack	Cat.Nos	Single television sockets
		For DVBT, cable cast and satellite installation (with individual demodulator) DVBT HDTV compatible TV: male connector (Ø9.5 mm) R: female connector (Ø9.5 mm) SAT: "F" type connector Recommended coaxial cable 17 VATC
		Female TV sockets - star attenuation < 1 dB TV: 0-2400 MHz Installation recommended in flush-mounting box depth 40 mm
5	2 811 51BA	 <ul style="list-style-type: none"> Brushed Aluminium Brushed Black Champagne Dark Bronze Dark Silver Matt Black Matt White
5	2 811 51BB	
5	2 811 51CH	
5	2 811 51DB	
5	2 811 51DS	
5	2 811 51MB	
10	2 811 51MW	
		Male TV sockets - star attenuation < 1.5 dB TV: 0-2400 MHz Installation recommended in flush-mounting box depth 40 mm
5	2 811 54BA	 <ul style="list-style-type: none"> Brushed Aluminium Brushed Black Champagne Dark Bronze Dark Silver Matt Black Matt White
5	2 811 54BB	
5	2 811 54CH	
5	2 811 54DB	
5	2 811 54DS	
5	2 811 54MB	
10	2 811 54MW	
		TV sockets "F" type with screws - star attenuation < 1 dB SAT: 0-2400 MHz
5	2 811 52BA	 <ul style="list-style-type: none"> Brushed Aluminium Brushed Black Champagne Dark Bronze Dark Silver Matt Black Matt White
5	2 811 52BB	
5	2 811 52CH	
5	2 811 52DB	
5	2 811 52DS	
5	2 811 52MB	
10	2 811 52MW	






2 810 31CH



2 810 21MB

Dimensions: 86 x 86 mm
Supplied with 2 screws M 3.5 for BS boxes
Supplied as complete product with protective film

Pack	Cat.Nos	Audio and video sockets
		Single loudspeaker sockets 4 mm ² terminals Brass connectors ensure excellent sound transmission quality
1	2 810 31BA	 <ul style="list-style-type: none"> Brushed Aluminium Brushed Black Champagne Dark Bronze Dark Silver Matt Black Matt White
1	2 810 31BB	
1	2 810 31CH	
1	2 810 31DB	
1	2 810 31DS	
1	2 810 31MB	
5	2 810 31MW	
		Double loudspeaker sockets 4 mm ² terminals Brass connectors ensure excellent sound transmission quality
1	2 810 32BA	 <ul style="list-style-type: none"> Brushed Aluminium Brushed Black Champagne Dark Bronze Dark Silver Matt Black Matt White
1	2 810 32BB	
1	2 810 32CH	
1	2 810 32DB	
1	2 810 32DS	
1	2 810 32MB	
5	2 810 32MW	
		HDMI Type-A sockets + USB Type-A data sockets Used to bring connections closer to the users and to transmit high-definition digital audio video streams between a source (Blu-Ray player, computer) and a compatible receiver (e.g. TV, videoprojector) and with connecting USB devices (interactive white board, scanner-printer, external hard disk)
1	2 810 21BA	 <ul style="list-style-type: none"> Brushed Aluminium Brushed Black Champagne Dark Bronze Dark Silver Matt Black Matt White
1	2 810 21BB	
1	2 810 21CH	
1	2 810 21DB	
1	2 810 21DS	
1	2 810 21MB	
5	2 810 21MW	