

Synergy™

hotel equipment - Sleek Design



Sleek design

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat.Nos	Shaver sockets
		Conform to BS EN 61558-2-5 Suitable for use with European, British, American and Australian 2 pin plugs Rating: 20 VA IP 24 Screwless live and neutral terminals For flush-mounting, back box to be min. 45 mm deep Supplied with 2-gang side extension (3 mm thick) in case of extra wiring space needed Nominal plate dimensions: 146 x 86 mm
1	8 320 90	<ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 90	
1	8 324 90	

Pack	Cat.Nos	Key card switches 230 V~
		For energizing a circuit by inserting a key fob or a smart card (access card for hotel rooms) Example of use: Hotel room power supply only when guest is present Time delay of approx. 30 sec. after card removal to be equipped with a single pole latching relay or contactor
1	8 321 00	<ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 323 00	
1	8 325 00	

Pack	Cat.Nos	Hotel call indicators DND/Please clean up
		Indicator for corridor Indicator lamp and bell push Installed in the corridor, displays calls
1	8 321 01	<ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 323 01	
1	8 325 01	

Pack	Cat.Nos	Hotel call indicators - internal room control
		Internal Control Unit Allow the user to select the desired setting supplied with LED
1	8 321 02	<ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 323 02	
1	8 325 02	

Synergy™

blanking plates, cord outlets - Sleek Design



8 320 95

8 322 96

8 320 52

Sleek design

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Pack	Cat.Nos	Blanking plates
		1-gang Nominal plate dimensions: 86 x 86 mm
1	8 320 95	<ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 95	
1	8 324 95	
		2-gang Nominal plate dimensions: 86 x 146 mm
1	8 320 96	<ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 96	
1	8 324 96	
		Cord outlets
		1-gang Nominal plate dimensions: 86 x 86 mm
1	8 320 52	<ul style="list-style-type: none"> ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 322 52	
1	8 324 52	

IP 55 splash-proof cover p. 721

