



BT-KW4141USB

Cover plates selection chart p. 760
Plates selection chart p. 778

To be equipped with a support frame, a cover plate and a plate
Socket outlets: shuttered for child safety

Pack	Cat.Nos	Socket outlets 16 A - 250 V~ + USB Type-C charger
1	BT-KW4141USB	<p>Conform to IEC 60884-3-1 and ETSI EN 301489-34 standards. For plugging and/or quick charging of devices USB Type-C charger, 1.5 A - 5 V - 7.5 W. Automatic terminals, screw fixing. Self-protected against power surges. 2 modules. Supplied with a support frame.</p> <p>2P+E German standard socket outlet</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand <p>2P+E French standard socket outlet</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand
1	BT-KG4141USB	
1	BT-KM4141USB	
1	BT-KW4142USB	<p>Conform to IEC 60884-3-1 and NEMA WD-6 standards. For plugging and/or quick charging of devices 2 x USB Type-A charger, 3 A 5 V - 15 W. 3 modules.</p> <p>2P+E Euro-US standard socket outlet 16 A</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand <p>2P+E American standard socket outlet 15 A</p> <p>When the plug is inserted, the socket surface slides inside the casing; it returns to its initial position when the plug is taken out.</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand
1	BT-KG4185AA	
1	BT-KM4185AA	
1	BT-KW4188AA	<p>Conform to IEC 60884-3-1 and NEMA WD-6 standards. For plugging and/or quick charging of devices 1 USB Type-A charger and 1 USB Type-C charger, 3 A - 5 V - 15 W. 3 modules.</p> <p>2P+E Euro-US standard socket outlet - 16 A</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand <p>2P+E American standard socket outlet - 15 A</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand
1	BT-KG4185AC	
1	BT-KM4185AC	
1	BT-KW4188AC	<p>Conform to IEC 60884-3-1 and NEMA WD-6 standards. For plugging and/or quick charging of devices 1 USB Type-A charger and 1 USB Type-C charger, 3 A - 5 V - 15 W. 3 modules.</p> <p>2P+E Euro-US standard socket outlet - 16 A</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand <p>2P+E American standard socket outlet - 15 A</p> <ul style="list-style-type: none"> ○ White ● Black ● Sand
1	BT-KG4188AC	
1	BT-KM4188AC	



BT-K4288C2



BT-K4191CC



BT-K4191AC

Cover plates selection chart p. 760
Plates selection chart p. 778

To be equipped with a support frame, a cover plate and a plate
Conform to IEC 62368-1 (Safety) and ETSI EN 301489-34 standards

Pack	Cat.Nos	USB chargers Type-C - Power Delivery
1	BT-K4192C	<p>Conform to IEC 62368-1 standards. For quick charging of devices such as smartphones, tablet PCs and Powerbanks. Standby consumption: < 0.07 W - 230 V - 5 V~.</p> <p>1 USB - Type-C - 3 A / 20 W Power Delivery</p> <p>1 module</p>
1	BT-K4288C2	<p>1 USB - Type-C - 3 A / 30 W Power Delivery</p> <p>2 modules</p>
1	BT-K4294C	<p>1 USB - Type-C - 3 A / 45 W Power Delivery</p> <p>2 modules</p>
1	BT-K4191CC	<p>Double USB charger Type-C</p> <p>Conform to IEC 62368-1 standards. For quick charging of devices such as smartphones, tablet PCs and Powerbanks. Standby consumption: < 0.1 W 100-240 V~ - 5 V~.</p> <p>2 USB - Type-C - 3 A / 15 W</p> <p>1 module</p>
1	BT-K4191A	<p>USB chargers Type-A</p> <p>Conform to IEC 62368-1 standards. For charging devices such as smartphones, tablet PCs and Powerbanks. Standby consumption: < 0.1 W 100-240 V~ - 5 V~.</p> <p>1 USB - Type-A - 3 A / 15 W</p> <p>1 module</p>
1	BT-K4191AA	
1	BT-K4191AC	<p>Double USB charger Type-A + Type-C</p> <p>For charging devices such as smartphones, tablet PCs and Powerbanks. Standby consumption: < 0.1 W 100-240 V~ - 5 V~.</p> <p>1 USB Type-A + 1 USB Type-C - 3 A / 15 W</p> <p>1 module</p>