

# Netatmo connected safety devices

smart cameras, video alarm system and door and window sensors



Home + Security



NA-NOC-PRO



NA-NOC-S-PRO



NA-NSC-PRO



NA-NBU-AS-PRO



NA-DTG-PRO

Pack	Cat.Nos	Smart outdoor camera
1	NA-NOC-PRO <sup>1</sup>	Smart outdoor safety camera with detection of people, animals and vehicles Aluminium single monobloc construction Ultra-resistant glass and plastic, protection against UV rays Video sensor: 4MP. Resolution: Full HD 1080 p. Coding: H.264. Long-range detection: up to 20 m Field of view: 100°. 8x digital zoom for videos. Video live microphone LED spotlight: 12 W, variable intensity Infrared night vision: 15 m. Encryption protected access to the smartphone using the Home + Security App. Weather resistant: designed for outdoor use (HZO protection)

1	NA-NOC-S-PRO <sup>1</sup>	<b>Smart outdoor camera with siren</b> Smart outdoor safety camera with detection of people, animals and vehicles Equipped with 105 db alarm siren Aluminium single monobloc construction Ultra-resistant glass and plastic, protection against UV rays Video sensor: 4MP. Resolution: Full HD 1080 p. Coding: H.264. Long-range detection: up to 20 m. Field of view: 100°. 8x digital zoom for videos. Video live microphone LED spotlight: 12 W, variable intensity Infrared night vision: 15 m Encryption protected access to the smartphone using the Home + Security App. Weather resistant: designed for outdoor use (HZO protection)
---	---------------------------	--

Pack	Cat.Nos	Smart indoor camera
1	NA-NSC-PRO <sup>1</sup>	Smart indoor safety camera with people detection consisting of an aluminium monobloc unit Video sensor: 4MP. 130° panoramic view for a wider coverage High quality video with Full HD 1080 p viewing Guaranteed day and night protection with infrared vision, for comfortable viewing even in total darkness Recording only in case of intrusion, in respect of the privacy of the family Encryption protected access to the smartphone using the Home + Security App. Declaration of conformity and FCC declarations Open-source compatibility It has to be connected to an electric socket with the supplied AC adapter

1	NA-NBU-AS-PRO <sup>1</sup>	<b>Smart video alarm system</b> Smart video security alarm system consisting of 1 smart indoor camera, 1 smart indoor siren and 3 smart door and window opening sensors The products can be easily configured and associated using the Home + Security app. The smart video alarm system activates and deactivates automatically, has pre-recorded sounds to simulate a presence in the home, respects the privacy of the family and activates a 110 dB sound in case of intrusion
---	----------------------------	--

1	NA-DTG-PRO <sup>1</sup>	<b>Smart door and window sensors</b> Smart opening sensors for doors and windows ideal for safety Sensors with waterproof monobloc construction, vibration/motion detection and open/closed status Power supply with 2 AAA-type batteries included in the package. They only work with the smart indoor camera (sold separately): radio link between the sensors and the camera. Declaration of conformity and FCC Open-source compatibility Can be controlled and managed remotely with Home + Security app.
---	-------------------------	--

<sup>1</sup>: The products available in your country are subject to local regulations. The Catalogue numbers may be different from those presented in the international catalogue. Please contact your local agency

