

Multifunction multi-outlet extensions (continued)



Multifunction multi-outlet extensions



For indoor use only

Pack	Cat.Nos	Multi-outlet extensions for dedicated spaces
		Charging stations with wireless charger and USB ports - for bed corner and workstation 10 A - 230 V - 2300 W MAX Compact charging stations with 5 ports equipped with: - 2 x 2P+E flush socket outlets - wireless charger for 10.0 W Qi-certified smartphones (with non-slip surface and charging indicator). Direct view on screen while charging - USB Type-A and USB Type-C ports: 3.0 A - 5.0 V - 15 W MAX - black 3G 1.5 mm ² cord (length: 2 m) 3 6 945 00 ● Taupe/Dark Grey 3 6 945 06 ● White/Dark Grey
		TV multi-outlet extensions with cord, switch and SPD 16 A - 230 V - 3680 W MAX Special design for perfect integration and cable management in TV corner Equipped with: - 4 x 2P+E (16 A) and 4 x 2P socket outlets - 1 On/Off illuminated switch - 3G 1.5 mm ² cord (length: 2 m) Integrated surge protective device (SPD): protects electronic equipment against lightning strikes Indicator signalling the surge protective device status: - green LED: the multi-outlet extension is protected - LED off: the multi-outlet extension is not protected but functional Aluminum (metal) cover allowing the installation of another device on top of the multi-outlet extension 3 6 945 95 ● Black (2P socket outlets: 6 A) 3 6 945 15 ● Black (2P socket outlets: 2.5 A)
		Angled multi-outlet extensions 16 A - 230 V - 3680 W MAX Adapted design for perfect integration in kitchen or workstation angle Equipped with: - flush socket outlets angled 45° - cable management at the back - removable part at the back to pass the cable through Solutions without cord: to be cabled with a 3G 1.5 mm ² cord 5 6 945 02 ○ 3 x 2P+E - White/Alu finish With 1 m white cord 3G 1.5 mm ² Equipped with 2 USB Type-A and USB Type-C ports: 3.0 A - 5.0 V - 15 W MAX 5 6 945 04 ○ 3 x 2P+E - White/Alu finish Without cord Equipped with 2 USB Type-A and USB Type-C ports: 3.0 A - 5.0 V - 15 W MAX 5 6 945 01 ○ 4 x 2P+E - White With 1 m white cord 3G 1.5 mm ² 5 6 945 03 ○ 4 x 2P+E - White Without cord

Wireless power charging

- Products certified Qi-WPC*
Low-emission technology compatible with the ICNIRP specifications concerning protecting people against electromagnetic fields
This wireless technology makes it possible to do away with cords and connectors
- Global standard
Adopted by the car industry and CHRs (Cafés/Hotels/Restaurants)
Incorporated in 100% of Qi-enabled smartphones
Average charging time < 2 hrs

Main compatible smartphones



See the full list on www.wirelesspowerconsortium.com


Brand	Range	Smartphone models
Apple	iPhone	13 / 12 / 11 / X / 8 / 8+
Samsung	Galaxy	S22 / S21 / S20 / S10 / S9 / S8 / S7 / S6 (Edge)
LG	G	V40 / V30 / G8 / G7 / G6 / G5 / G4 / G3
Sony	Xperia	Z4v / Z3v / XZ3 / XZ2

TV multi-outlet extension with cord, switch and surge protective device Cat.No 6 945 95/15

Example of implementation



Dimensions (in mm)



Opening system

