

Terminal products

for multimedia home network



Selection chart p. 873

RJ 45 sockets Mosaic

Pack	Cat.Nos	
10	0 765 61	Cat. 6 UTP - 1 module ○ White ● Aluminium ● Black Mat
10	0 794 61	
10	0 794 61L	
10	0 765 64	Cat. 6 UTP - 2 modules ○ White ● Aluminium ● Black Mat
10	0 794 64	
10	0 791 64L	

RJ 45 sockets Arteor

10	5 723 02	Cat. 6 UTP - 1 module ○ White ● Magnesium ● Champagne ● Soft Alu
10	5 728 02	
10	5 700 57	
10	5 710 57	
10	5 723 14	Cat. 6 UTP - 2 modules ○ White - square version ● Magnesium - square version ● Champagne - square version ● Soft Alu - square version
10	5 728 14	
10	5 700 59	
10	5 710 59	
10	5 723 24	Cat. 6 UTP - 2 modules ○ White - round version ● Magnesium - round version ● Soft Alu - round version
10	5 728 24	
10	5 728 24	
10	5 728 81	

PoE Wi-Fi Access point

1	0 336 10	<p>Flush-mounting To be installed in flush-mounting boxes min. depth 40 mm With RJ 45 connector with fast connection thanks to integrated crimping Power supply by a Power over Ethernet switch Easy configuration with a smartphone or computer (Home + Project or browser based) Possibility to choose Wi-Fi signal strength (only in room or beyond) ON/OFF function Wi-Fi 802.11n+ac</p>
1	0 335 23	<p>Surface-mounting Plug & play product to be installed on any RJ 45 socket connected to a Power over Ethernet switch Self powered with PoE Easy configuration with a smartphone or computer (Home + Project or browser based) Possibility to choose Wi-Fi signal strength (only in room or beyond) WPS (Wi-Fi Protected Setup) and ON/OFF functions Wi-Fi 802.11n</p>

RJ 45 patch cords and user cords

Pack	Cat.Nos	
		Cat. 6 unscreened impedance 100 Ω
		PVC
1	0 518 18	RJ 45 - RJ 45 right Length 0.5 m
1	0 517 72	Length 1 m
1	0 517 73	Length 2 m
1	0 517 74	Length 3 m
1	0 517 75	Length 5 m
		LSZH
1	0 518 62 0 518 58	Length 1 m
1	0 518 63 0 518 59	Length 2 m
1	0 518 64 0 518 60	Length 3 m
1	0 518 65 0 518 61	Length 5 m

		Optical sockets Mosaic
		For connecting 2 fibres to the workstation Equipped with 1 duplex adaptor Supplied with protective caps 2 modules
		SC/APC single mode fiber optic socket
1	0 786 14	○ White ● Aluminium ● Black Mat
1	0794 15L	
1	0791 14L	

5	0 326 18	Optical fiber cord
		For connecting 2 fibres to the workstation Equipped with 1 duplex adaptor Supplied with protective caps 2 modules