

Lighting Management

BUS/KNX false ceiling and modular controllers



Connected with the BUS/KNX cable
Configuration using ETS programming software

Pack	Cat.Nos	False ceiling controllers for dimming	Pack	Cat.Nos	Modular ON/OFF controller
1	0 488 88	Each output can be controlled by a sensor and/or BUS/KNX control unit For DALI control 4 outputs 32 ballasts maximum per output	1	0 026 80	Each output can be controlled by a sensor and/or BUS/KNX control unit 4 x 16 A outputs 4 DIN modules
1	0 488 87	For 1-10V control 4 outputs 1000 VA maximum per output Also control 4 ON/OFF circuits			Modular multi-applications ON/OFF controllers
		Modular controllers for dimming			Each output can be controlled by a sensor and/or BUS/KNX control unit Multi-applications controllers with independent input channels and outputs configurable to control lighting loads, power sockets, roller shutters, and HVAC equipment
1	0 026 65	Each output can be controlled by a sensor and/or BUS/KNX control unit For DALI control 1 output DALI bus (64 DALI ballasts max) to control up to 16 DALI groups and up to 64 DALI scenes 4 DIN modules	1	0 026 72	8 x 16 A outputs 6 DIN modules
1	0 026 99	1 output DALI bus (64 DALI ballasts max) to control individually up to 64 DALI luminaires and up to 16 DALI scenes 4 DIN modules	1	0 026 73	8 x 16 A outputs - 8 inputs 6 DIN modules
1	0 026 68	For 1-10V control 10 outputs 1-10 V also controlling 10 ON/OFF circuits (16 A max) 10 DIN modules	1	0 026 74	12 x 16 A outputs 6 DIN modules
1	0 026 54	For LED and all others LV and ELV loads 2 outputs 2 x 300 W/VA maximum per output 4 DIN modules	1	0 026 76	16 x 16 A outputs 10 DIN modules
1	0 026 86	For LV and ELV loads only 2 outputs 2 x 500 VA maximum per output	1	0 026 78	20 x 16 A outputs 10 DIN modules
1	0 026 87	8 DIN modules 4 outputs 4 x 500 VA maximum per output 12 DIN modules	1	0 026 79	20 x 16 A outputs - 18 inputs 10 DIN modules
					Room Controller Unit Power modules equipped with output contacts for controlling: - different types of ON/OFF load (lighting, roller shutters, contactors, motors, etc.) - a DALI dimming output for 64 ballasts max. Loads are managed by the controls to which they are linked: either by BUS/KNX controls, or by wired connection input terminals (switches, push-buttons, volt-free contacts) Multiphase connection and consumption measurement
			1	0 484 18	8 inputs - 10 outputs 8 DIN modules
			1	0 484 22	16 inputs - 16 outputs 12 DIN modules