

Audio/video system

audio/video sockets (continued)



Pack	Cat.Nos		3.5 mm female Jack sockets
			For making audio links
			Preterminated sockets - 1 module
			Equipped with a 15 cm cord and 2 female connectors
1	Mosaic 0 787 79	Arteor 5 720 91	<ul style="list-style-type: none"> ○ White ● Aluminium ● Matt Black ● Magnesium ● Champagne ● Soft Alu
1	0 793 79		
1	0 795 79L		
1		5 725 91	
1		5 725 59	
1		5 725 55	
1	0 787 64	5 722 74	Screw-type sockets - 1 module
1	0 795 64L		<ul style="list-style-type: none"> ○ White ● Matt Black ● Magnesium ● Champagne ● Soft Alu
1		5 727 74	
1		5 724 91	
1		5 724 90	
1	0 787 73	5 722 78	Solder-type sockets - 1 module
			<ul style="list-style-type: none"> ○ White

Pack	Cat.Nos		2 female RCA sockets
			Provide the stereo audio link for any peripheral device such as a DVD player, camera, video recorder, etc.
			1 module
			Preterminated
			Equipped with a 15 cm cord and 2 female connectors
1	Mosaic 0 787 47	Arteor 5 720 92	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1		5 725 92	
1		5 724 79	
1		5 724 75	
1	0 787 53	5 722 72	Connection via screw terminals
1		5 727 72	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1		5 724 95	
1		5 724 94	

Pack	Cat.Nos		3 female RCA sockets
			Provide the stereo audio link and composite video for any peripheral device such as a DVD player, camera, video recorder, videoconferencing, etc.
			1 module
			Connection via screw terminals
1	Mosaic 0 787 54	Arteor 5 722 73	<ul style="list-style-type: none"> ○ White ● Aluminium ● Magnesium ● Champagne ● Soft Alu
1	0 792 54		
1		5 727 73	
1		5 724 97	
1		5 724 96	

Pack	Cat.Nos		3-pole XLR sockets
			Provide the stereo link for any peripheral device, microphone, amplifier, mixing console, etc.
			Recommended cable: 1 shielded audio pair 0.14 mm ² to 0.50 mm ²
			Max. cable length: 50 m (without amplifier)
			Fast screw connection
			2 modules
			Female sockets
1	Mosaic 0 787 55	Arteor 5 722 83	<ul style="list-style-type: none"> ○ White ● Aluminium ● Matt Black ● Magnesium ● Champagne ● Soft Alu
1	0 792 55		
1	0 795 55L		
1		5 727 83	
1		5 724 99	
1		5 724 98	
1	0 787 56	5 722 77	Male sockets
			<ul style="list-style-type: none"> ○ White

Pack	Cat.Nos		Speakon socket - 4 contacts
			To be used to connect powered speakers
			Recommended cable: 2 audio pairs 4 mm ² max.
			Max. cable length: 50 m (without amplifier)
			2 modules
1	Mosaic 0 787 60		<ul style="list-style-type: none"> ○ White

Pack	Cat.Nos		Loudspeaker sockets
			For loudspeaker stereo audio link
			4 mm ² terminal
			Sockets - 1 module
10	Mosaic 0 787 50	Arteor 5 722 70	<ul style="list-style-type: none"> ○ White ● Aluminium ● Matt Black ● Magnesium ● Champagne ● Soft Alu
10	0 792 50		
10	0 795 50L		
10		5 727 70	
10		5 726 97	
10		5 726 96	
10	0 787 51	5 722 80	Sockets - 2 modules
10	0 795 51L		<ul style="list-style-type: none"> ○ White ● Matt Black ● Magnesium ● Champagne ● Soft Alu
10		5 727 80	
10		5 726 99	
10		5 726 98	

Pack	Cat.Nos		100 V line attenuators
			25 W - 2 modules
			To be used to control the power from a 100 V PA system line
1	Mosaic 0 787 76	Arteor 5 722 84	<ul style="list-style-type: none"> ○ White ● Magnesium
1		5 727 84	

Pack	Cat.Nos		Female BNC 75 sockets - 1 module
			Provide the composite video link for any peripheral device such as a DVD player, camera, video recorder, etc.
1	Mosaic 0 787 58	Arteor 5 722 76	<ul style="list-style-type: none"> ○ White ● Magnesium
1		5 727 76	

USB Data socket,
See p. 1009

