

Legrand cabling system, LCS³ cat. 6

RJ 45 sockets - Mosaic™



Can be integrated in any support
Mechanisms to be equipped with support frames and plates
Equipped with connectors with quick toolless connection
Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
T568A and B marking with colour codes
Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

Pack	Cat.Nos	Cat. 6 RJ 45 sockets - Mosaic	Pack	Cat.Nos	Cat. 6 RJ 45 sockets - Mosaic (continued)
10	0 765 61	UTP - 1 module ○ White	5	0 765 95	FTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter
10	0 794 61	● Aluminium	10	0 765 05	FTP 45° - 2 modules ○ White
10	0 794 61L	● Matt Black	5	0 765 06	FTP 45° - 2 x RJ 45 - 2 modules ○ White
10	0 765 81	○ White antimicrobial ⁽¹⁾	1	0 765 33	FTP with retractable cord - 4 modules With integrated retractable cord (0.9 m) Automatically winds back in at the press of a button ○ White
10	0 765 64	UTP - 2 modules ○ White	1	0 794 33	● Aluminium
10	0 794 64	● Aluminium	10	0 765 92	FTP 90° - 2 modules Vertical snap-on socket for column module ○ White
10	0 791 64L	● Matt Black	10	0 794 92	● Aluminium
5	0 765 94	UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter	10	0 765 63	Shielded STP - 1 module ○ White
10	0 765 91	UTP 90° - 2 modules Vertical snap-on socket for column module ○ White	10	0 765 83	○ White antimicrobial ⁽¹⁾
10	0 765 03	UTP 45° - 2 modules ○ White	10	0 765 66	Shielded STP - 2 modules ○ White
5	0 765 04	UTP 45° - 2 x RJ 45 - 2 modules ○ White	5	0 765 96	Shielded STP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter
1	0 765 32	UTP with retractable cord - 4 modules With integrated retractable cord (0.9 m) Automatically winds back in at the press of a button ○ White	10	0 765 07	STP 45° - 2 modules ○ White
5	0 765 44	UTP 2 x RJ 45 with Soluclip accessory - 3 modules For snap-on mounting on DLP trunking with 45 mm cover ○ White	10	0 765 93	Shielded STP 90° - 2 modules Vertical snap-on socket for column module ○ White
10	0 765 62	FTP - 1 module ○ White			
10	0 794 62	● Aluminium			
10	0 791 62L	● Matt Black			
10	0 765 82	○ White antimicrobial ⁽¹⁾			
10	0 765 65	FTP - 2 modules ○ White			
10	0 794 65	● Aluminium			
10	0 791 65L	● Matt Black			
10	0 765 22	○ White with green shutter			
10	0 765 23	○ White with orange shutter			
5	0 765 46	FTP 2 x RJ 45 with Soluclip accessory - 3 modules For snap-on mounting on DLP trunking with 45 mm cover ○ White			

1: Contains a silver compound which prevents the growth of bacteria at the surface