



0 336 83



0 336 84



0 336 82



0 336 80



0 336 81



HDJ6A-44



HDJ6-44

Standard fixing  
 Universal mounting on all cabinets or enclosures  
 Panels ensure automatic earthing of each connector  
 Equipped with rear cable guides to hold cables during maintenance

Pack	Cat.Nos	Flat patch panels - to be equipped
1	0 336 83	<b>19" panels - 1U</b> Equipped with 4 automatically removable cassettes, takes up to 24 cat. 5e to cat. 6 <sub>A</sub> RJ 45 HD Jack connectors
1	0 336 84	Equipped with 4 automatically removable HD cassettes, takes up to 48 cat. 5e to cat. 6 <sub>A</sub> RJ 45 HD Jack connectors
<b>Empty flat patch panels - to be equipped</b>		
1	0 336 82	<b>19" panel - 1 U - standard fixation</b> Takes a maximum of 4 automatically removable cassettes to be equipped with up to 24 cat. 5e to cat. 6 <sub>A</sub> RJ 45 HD Jack connectors
1	0 337 91	<b>19" panel - 1 U - automatic fixation (Soluclip)</b> Takes a maximum of 4 automatically removable cassettes to be equipped with up to 24 cat. 5e to cat. 6 <sub>A</sub> RJ 45 HD Jack connectors
<b>Cassettes for flat panels to be equipped</b>		
Can be removed by simple pressing on the cassette, for ease of installation and maintenance For equipping flat panels		
1	0 336 80	Removable empty cassette to be equipped with connectors, takes 6 cat. 5e to cat. 6 <sub>A</sub> RJ 45 HD Jack connectors
1	0 336 81	Removable empty cassette to be equipped with connectors, takes 12 cat. 5e to cat. 6 <sub>A</sub> RJ 45 HD Jack connectors
<b>Blanking cassette</b>		
1	0 336 85	To be used to fill gaps in the panel

Pack	Cat.Nos	RJ 45 HD Jack connectors
Quick-connect connection (no tools required) T568A and B marking with colour codes Compliant with following standards: ISO/IEC 11 801; EN 50173; ANSI/TIA-568-C.2; UL 1863 (and UL 2043 for Cat.Nos HDJS); IEEE 802.3af/802.3at/802.3bt Type 1 to Type 4; FCC part 68 subpart F; IEC-603-7 Intertek ETL Verified component To be installed in cassettes Cat.Nos 0 336 80 and 0 336 81 for flat panels Set of 20 connectors except for Cat.Nos HDJS625 and HDJS6A25 (set of 25 connectors)		
<b>Cat. 6<sub>A</sub> RJ 45 HD Jack connectors</b>		
20	HDJ6A-00	UTP - Black
20	HDJ6A-36	UTP - Blue
20	HDJ6A-44	UTP - Yellow
25	HDJS6A25	STP
<b>Cat. 6 RJ 45 HD Jack connectors</b>		
20	HDJ6-00	UTP - Black
20	HDJ6-36	UTP - Blue
20	HDJ6-44	UTP - Yellow
20	HDJ6-88	UTP - White
25	HDJS625	STP
<b>Cat. 5e RJ 45 HD Jack connector</b>		
20	HDJ5E-78	UTP - Dark gray
<b>Blank module for RJ 45 HD Jack connectors</b>		
10	HDJBL10-00	HDJ - Black