

# Audio/video system

## audio/video sockets



Pack	Cat.Nos		Type-A HDMI sockets
			For transmitting High Definition digital audio/video streams between a source (computer, DVD or Blu-Ray player, etc) and a compatible receiver (TV, video projector, etc.) Max. length between 2 sockets: 10 m
			<b>HDMI 2.0 preterminated sockets - 1 module</b> Equipped with a 15 cm cord and 2 female connectors
1	Mosaic 0 787 78	Arteor 5 720 96	<ul style="list-style-type: none"> <li>○ White</li> <li>● Aluminium</li> <li>● Matt Black</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	0 793 78		
1	0 794 78L		
1		5 725 96	
1		5 725 18	
1		5 725 17	
			<b>HDMI 2.0 preterminated sockets - 2 modules</b>
1	0 789 79L	5 722 99	<ul style="list-style-type: none"> <li>○ White</li> <li>● Aluminium</li> <li>● Matt Black</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	0 792 79L		
1	0 794 79L		
1		5 725 99	
1		5 723 46	
1		5 723 45	
			<b>HDMI audio/video extender</b>
1	0 517 38		<p>For connecting HDMI terminals up to 60 m apart The kit comprises transmitter and receiver units as well as power supplies The transmitter and receiver are linked by an RJ 45/RJ 45 cable (not supplied) Compatible with 4K, 3D, EDID and HDCP Infrared controller included Certified HDBaseT</p>
			<b>Display Port sockets</b>
			For transmitting High Definition digital audio/video streams between a source (laptop computer, DVD or Blu-Ray player, etc) and a compatible receiver (video projector, TV, etc.) Max. length between 2 sockets: 10 m Preterminated sockets - 1 module Equipped with a 15 cm cord and 2 female connectors
1	Mosaic 0 787 91	Arteor 5 720 90	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> </ul>
1		5 725 90	

Pack	Cat.Nos		Female HD15 sockets
			For transmitting analogue video streams between a source (computer) and a compatible receiver (video projector, TV, computer screen, etc.) VGA to UXGA resolution Max. length between 2 sockets: 15 m
			<b>Preterminated sockets - 1 module</b> Equipped with a 15 cm cord and 2 female connectors
1	Mosaic 0 787 77	Arteor 5 720 97	<ul style="list-style-type: none"> <li>○ White</li> <li>● Aluminium</li> <li>● Magnesium</li> </ul>
1	0 793 77		
1		5 725 97	
			<b>Screw-type sockets - 2 modules</b>
1	0 787 57	5 722 82	<ul style="list-style-type: none"> <li>○ White</li> </ul>
			<b>Screw-type sockets + 3.5 mm Jack - 2 modules</b>
1	0 787 74	5 722 88	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> </ul>
1		5 727 88	
			<b>Infrared ON/Standby controls for video projector</b>
			To be used to switch on a video projector or set it to standby Must be combined with a push-button Work with any infrared video projector or other product with an infrared remote control (TV, air conditioning, games console, etc.) using a learning process Installed near the switch controlling the lighting in a room, the push-button sends the command to the IR ON/Standby control which replaces the manufacturer's remote control and makes it easier to switch the video projector on and off
1	Mosaic 0 787 99		<ul style="list-style-type: none"> <li>○ White</li> </ul>

1: Can be installed in receptacles for floor sockets

