

Mosaic™ mechanisms

USB charging sockets and Mosaic Link USB charging sockets



0 776 90L

0 776 82L

0 791 90L

0 793 94

0 776 70L

Selection chart for boxes, supports and plates p. 1198-1199

Conform to IEC 62684-2011-01. Class II SELV
Surge protection > 1 kV. Power supply AC/DC efficiency level: VI.
Standby consumption: < 0.07 W - 230 V - 5 V_{DC}
2 x 2.5 mm² screw terminals (except for Cat.Nos 0 776 7XL and Mosaic Link charging sockets)
Supplied cordless

Pack	Cat.Nos	USB charging sockets Type-C - Power Delivery
		For quick charging of devices such as smartphones, laptops, tablets and Powerbanks
		Single USB - Type-C - 20 W - 1 module For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings Not compatible with Batibox flush-mounting box
1	0 776 90L	○ White
1	0 776 92L	● Matt black
1	0 776 91L	● Alu
		Single USB - Type-C - 30 W - 2 modules
1	0 775 85L	○ White
1	0 793 85L	● Matt black
1	0 791 85L	● Alu
		Single USB - Type-C - 45 W - 2 modules Ideal for laptop charging
1	0 776 55L	○ White
1	0 776 57L	● Matt black
1	0 776 56L	● Alu
		Double USB - Type-C - 30 W - 2 modules For charging devices such as smartphones and laptops
1	0 776 31L	○ White
1	0 776 33L	● Matt black
1	0 776 32L	● Alu
		Double USB - Type-C - 63 W - 3 modules For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings Ideal for laptop charging Automatic terminals
1	0 776 73L	○ White
1	0 776 75L	● Matt black
1	0 776 74L	● Alu

Pack	Cat.Nos	USB charging sockets Type-C
		For charging devices such as smartphones, laptops, tablets and Powerbanks
		Single USB - Type-C - 1.5 A / 7.5 W - 1 module
1	0 775 89	○ White
1	0 791 89L	● Matt black
1	0 793 89	● Alu
		Double USB - Type-C - 3 A / 15 W - 1 module For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings Not compatible with Batibox flush-mounting box
1	0 776 80L	○ White
1	0 776 82L	● Matt black
1	0 776 81L	● Alu
		Double USB - Type-C - 3 A / 15 W - 2 modules
1	0 775 90	○ White
1	0 791 90L	● Matt black
1	0 793 90	● Alu

Pack	Cat.Nos	USB charging sockets Type-A
		For charging devices such as smartphones, laptops, tablets and Powerbanks
		Single USB - Type-A - 1.5 A / 7.5 W - 1 module
1	0 775 91	○ White
1	0 793 91	● Alu
		Single USB - Type-A - 3 A / 15 W - 1 module For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings Not compatible with Batibox flush-mounting box
1	0 776 50L	○ White
1	0 776 52L	● Matt black
1	0 776 51L	● Alu
		Double USB - Type-A - 3 A / 15 W - 1 module For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings Not compatible with Batibox flush-mounting box
1	0 776 60L	○ White
1	0 776 62L	● Matt black
1	0 776 61L	● Alu
		Double USB - Type-A - 3 A / 15 W - 2 modules
1	0 775 94	○ White
1	0 791 94L	● Matt black
1	0 793 94	● Alu
		USB charging sockets Type-A + Type-C
		For charging devices such as smartphones, laptops, tablets and Powerbanks
		Double USB - Type-A + Type-C - 3 A / 15 W - 1 module For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings Not compatible with Batibox flush-mounting box
1	0 776 70L	○ White
1	0 776 72L	● Matt black
1	0 776 71L	● Alu
		Double USB - Type-A + Type-C - 3 A / 15 W - 2 modules
1	0 775 92	○ White
1	0 793 92	● Alu

Pack	Cat.Nos	Mosaic Link USB charging sockets - Type-A + Type-C - 3 A - 15 W - 2 modules
		Used to connect a device and fast charge a tablet or smartphone. With side connection via bistable automatic terminals For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions, DLP trunkings and flush-mounting boxes depth 50 mm Can be combined with other Mosaic Link sockets using a connection accessory (supplied)
10	0 775 70L	○ White
10	0 791 93L	● Matt black
10	0 792 93L	● Alu