

Mosaic™ mechanisms

telephone sockets



0 792 38



0 787 32



Selection chart for boxes, supports and plates **p. 1198-1199**

Pack	Cat.Nos	Telephone sockets
10	0 787 38	8-contact sockets <ul style="list-style-type: none"> ○ White - 2 modules ● Alu - 2 modules
10	0 792 38	
10	0 787 30	RJ 11 and RJ 12 sockets Equipped with a modular Jack connector with 1/4 turn terminal for fast connection. Tap-off possible <ul style="list-style-type: none"> ○ White - RJ 11, 4 contacts - 1 module ● Alu - RJ 11, 4 contacts - 1 module
10	0 792 31	
10	0 787 31	<ul style="list-style-type: none"> ○ White - RJ 11, 4 contacts - 2 modules
10	0 787 32	<ul style="list-style-type: none"> ○ White - RJ 12, 6 contacts - 2 modules

Mosaic™ mechanisms

television sockets



0 787 95



0 791 86L



0 787 86



0 787 94



0 787 93



Selection chart for boxes, supports and plates **p. 1198-1199**
 Technical characteristics see **e-catalogue**

For DVBT, Cablecast and satellite installation
 UHD TV compatible
 Class A shielded star sockets LTE Ready (4G protected)
 Recommended coaxial cable: 17 VATC
 Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch). Visual checking of the connection
 Meet EN 50083 standards and European directive EM 50083-2
 Low attenuation: 1.5 dB
 TV: male connector (Ø9.5 mm) - 5-68 / 230-862 MHz
 R: female connector (Ø9.5 mm) - 87.5-108 MHz / DAB 174-223 MHz
 SAT: "F type" connector - 950-2400 MHz

Pack	Cat.Nos	Multi TV star sockets
5	0 787 95	TV-SAT - 1 module <ul style="list-style-type: none"> ○ White
10	0 787 86	TV-R-SAT - 2 modules <ul style="list-style-type: none"> ○ White ● Alu ● Matt Black
10	0 792 96	
10	0 791 86L	
10	0 787 94	TV-R-SAT - SAT - 2 modules <ul style="list-style-type: none"> ○ White (In1: TV-R-SAT / In2: SAT 2)
5	0 787 93	Single TV star sockets TV Ø9.5 mm male <ul style="list-style-type: none"> ○ White - 1 module
10	0 787 82	<ul style="list-style-type: none"> ○ White - 2 modules ● Alu - 2 modules ● Matt Black - 2 modules
10	0 792 92	
10	0 791 82L	
10	0 787 90	TV "F-type" <ul style="list-style-type: none"> ○ White - 1 module
10	0 787 80	<ul style="list-style-type: none"> ○ White - 2 modules
10	0 787 83	Other TV socket TV-R socket For installation maintenance <ul style="list-style-type: none"> ○ White - 2 modules