

# Mosaic™ mechanisms

keyswitches, emergency stop push-buttons, keycard switches, hotel bedroom indicators and shaver socket



Selection chart for boxes, supports and plates **p. 1198-1199**

Pack	Cat.Nos	Keyswitch for emergency lighting luminaires	Pack	Cat.Nos	Emergency stop mushroom head push-buttons (continued)
1	0 766 30	<p>For simultaneous remote control: switching off the normal lighting and setting the emergency lighting to rest mode Can be used to multiply the number of control points for setting the building to rest mode (eg: one per access point) Must be used in addition to multifunction remote control unit 0 625 20/21 2 modules</p> <p>○ White</p>	1	0 766 02	<p><b>1/4 turn</b> NO + NC - 3 A - 250 V~ - 1/4 turn unlocking ● Red/yellow</p>
1	0 770 72	<p><b>Keyswitches</b> 2 modules</p> <p><b>2-position switch</b> By changeover contact 6 A - 250 V~ RONIS key no. 601 Key can be removed in both positions</p> <p>○ White</p>	1	0 767 28	<p><b>Keycard switches</b> For energizing a circuit by inserting an ISO format card (e.g: Cat.No 0 767 11 or hotel room access card) Time-delay: 30 sec. after card removal Backlight insert badge area 2 modules</p> <p><b>Electronic keycard switches</b> Only operates with MIFARE contactless ISO badge cards (e.g Cat.No 0 767 11 p. 518) Contact capacity: - 110 V, power 15 VA - 230 V, power 30 VA</p>
1	0 770 73	<p><b>3-position switch</b> Changeover switch with OFF position 6 A - 250 V~ RONIS key no. 601 Key can be removed in all 3 positions</p> <p>○ White</p>	1	0 784 45	<p><b>Mechanical keycard switches</b> Operate via contact with ISO card or key fob Cat.No 0 898 06 Contact capacity: - 110 V, power 15 VA - 230 V, power 30 VA</p> <p>○ White ● Matt Black</p>
1	0 770 74	<p><b>2-position switch - European key barrel</b> 1 contact - 2 poles 10 A - 250 V~ Key extracted in central position without changing the status of the contacts ON/OFF Must be fitted with standard European key barrel or key barrel Cat.No 0 697 95</p> <p>○ White</p>	10	0 898 06	<p><b>Key fob</b> Supplied complete with a label holder for individual hotel identification</p>
1	0 770 75	<p><b>3-position push-button - European key barrel</b> Changeover switch with OFF position 10 A - 250 V~ Key extracted in OFF position Must be fitted with standard European key barrel or key barrel Cat.No 0 697 95</p> <p>○ White</p>	5	0 770 47	<p><b>Hotel bedroom indicators</b> Indicator lamp and bell push Enable the resident to inform hotel staff of the room status 2 settings available: Do not disturb / Please clean the room Installed in the corridor, displays calls Supplied with lamps</p>
1	0 697 95	<p><b>European key barrel</b> European key barrel supplied with one set of 3 keys</p>	5	0 770 48	<p>Allows the user to select the desired setting Supplied with lamp Cat.No 0 676 68</p>
1	0 766 01	<p><b>Emergency stop mushroom head push-buttons</b> 2 modules</p> <p><b>With key</b> NO + NC 3 A - 250 V~ Unlock with RONIS key no. 455</p> <p>● Red/yellow</p>	1	0 775 86	<p><b>Shaver socket IP 24 - IK 04</b> Conform to EN 60742 and EN 61558-2 Power supply 230 V~ - 50/60 Hz and 1 output 120/220 V~ Connection via automatic terminals Equipped with a circuit separation transformer to isolate the user from the mains supply Protected against overloads and short circuits by built-in thermal relay limiting the available power to 20 VA Insertion of the plug activates the power supply to the transformer</p> <p>With integrated support For flush mounting 2 gang boxes only, 40 mm deep 5 modules</p>