

commercial floor trunking systems

flush lid floor trunking



Dimensions and technical information **p. 54**
Installation details **p. 55**

Body and lid manufactured from pre-galvanised sheet steel to BS EN 10346
Standard length : 2.0 m body / 500 mm lid
Standard lid thickness : 2.5 mm
Supplied complete with all necessary connectors and screws
Internal dividers are fitted on all trunking lengths 225 mm and above to provide lid support

Service outlet boxes are not available for this range

Pack	Cat. Nos.	Flush lid floor trunking	
		Trunking length – 2 m	
1	FF42	100 x 50 mm	
1	FF63	150 x 75 mm	
1	FF124	300 x 100 mm	
		90° riser bend	
		Supplied with screeding cover Provides conduit entry with 20 mm knockouts	
1	FFRB42	100 x 50 mm	
1	FFRB63	150 x 75 mm	
1	FFRB124	300 x 100 mm	
		End stop	
1	FFEB42	100 x 50 mm	
1	FFEB63	150 x 75 mm	
1	FFEB124	300 x 100 mm	
		Junction box	
		Supplied with connectors and blanking plates To be configured as a fourway, tee, bend or straight through connector box	
1	FFI42	100 x 50 mm	
1	FFI63	150 x 75 mm	
1	FFI124	300 x 100 mm	

commercial floor trunking systems

recessed lid floor trunking



Dimensions and technical information **p. 54**
Installation details **p. 55**

Body and lid manufactured from pre-galvanised sheet steel to BS EN 10346
Standard length : 2.0 m body / 500 mm lid
Standard lid thickness : 2.5 mm
Lid recess : 3.5 mm
Supplied complete with all necessary connectors and screws
Internal dividers are fitted on all trunking lengths 225 mm and above to provide lid support

Service outlet boxes are not available for this range

Pack	Cat. Nos.	Recessed lid floor trunking	
		Trunking length – 2 m	
1	FRL42	100 x 50 mm	
1	FRL63	150 x 75 mm	
1	FRL124	300 x 100 mm	
		90° riser bend	
		Supplied with screeding cover Provides conduit entry with 20 mm knockouts	
1	FRLRB42	100 x 50 mm	
1	FRLRB63	150 x 75 mm	
1	FRLRB124	300 x 100 mm	
		End stop	
1	FRLEB42	100 x 50 mm	
1	FRLEB63	150 x 75 mm	
1	FRLEB124	300 x 100 mm	
		Junction box	
		Supplied with connectors and blanking plates To be configured as a fourway, tee, bend or straight through connector box	
1	FRLI42	100 x 50 mm	
1	FRLI63	150 x 75 mm	
1	FRLI124	300 x 100 mm	

Flush lid and recessed lid floor trunking can be supplied in other widths, depths and compartment configurations to special order
Contact us on +44 (0) 370 608 9020

