


access floor service outlet boxes

accessory plates and ancillary items



 Selection charts **p. 26-29**
Dimensions and technical information **p. 33**

Lid and trim mouldings are precision engineered from hard wearing durable ABS. Lid is reinforced with a galvanised mild steel plate
Mounting frame and box base - 0.9 mm thick galvanised steel
Each compartment has 2 entries for 20 mm and 2 entries for 25 mm flexible conduits
Grey mouldings. Alternative colours available to special order. Grey plates
2, 3 and 4 compartment boxes are also available with separate individual compartment base units for convenient offsite pre-wiring
Supplied in parts or fully assembled and configured to customer specification
Conform to BS EN 61534-22

Pack	Cat. Nos.	1, 2 and 3 compartment accessory plates
		100 mm width
1	CR020	Blank plate
1	CR022	2 gang switched socket outlet
1	CR023	2 gang switched socket outlet, low noise / clean earth
1	CR027	2 gang non-standard switched socket outlet
1	CR029	2 gang unswitched socket outlet
1	CR030	3 gang unswitched socket outlet
1	CR044	3 gang unswitched socket outlet, low noise / clean earth
1	CR036	2 gang RCD 30 mA socket outlet
1	CR043	2 gang RCD 30 mA socket outlet, low noise / clean earth
1	CR047	100 mm plate – 2 gang RCD 30 mA switched shallow socket outlet specifically for 75 mm deep floor boxes
1	CR048	100 mm plate – low noise 2 gang RCD 30 mA switched shallow socket outlet specifically for 75 mm deep floor boxes
1	CR026	Punched plate for 2 x 1 gang accessories (60.3 mm fixing centres)
1	CR028	Punched plate for 2 gang accessories (120.6 mm fixing centres)
1	CR042	Angled punched plate for 4 x RJ45 (37 mm x 22 mm cut-outs)
1	CR031	2 x LJ2 accessory plate (50 mm fixing centres)
1	CR033	4 x BNC connector plate
1	CR024	4 x Data / telecoms plate (37 mm x 22 mm cut-outs)
1	CR025	6 x Data / telecoms plate (37 mm x 22 mm cut-outs)
1	CR035	100 mm plate for 2 x 50 mm x 50 mm Euro Module
1	CR070	100 mm plate for 3 x 45 mm x 45 mm Arteor modules

Pack	Cat. Nos.	4 compartment accessory plates
		75 mm compartment widths
1	CR4100	Blank plate
1	CR4101	2 gang switched socket outlet
1	CR4102	2 gang switched socket outlet, low noise / clean earth
1	CR4103	2 gang non-standard switched socket outlet
1	CR4104	2 gang unswitched socket outlet
1	CR4105	3 gang unswitched socket outlet
1	CR4118	3 gang unswitched socket outlet, low noise / clean earth

Pack	Cat. Nos.	4 compartment accessory plates (continued)
		75 mm compartment widths
1	CR4111	2 gang RCD 30 mA socket outlet
1	CR4117	2 gang RCD 30 mA socket outlet, low noise / clean earth
1	CR4128	75 mm plate – 2 gang RCD 30 mA switched shallow socket outlet specifically for 75 mm deep floor boxes
1	CR4129	75 mm plate – low noise 2 gang RCD 30 mA switched shallow socket outlet specifically for 75 mm deep floor boxes
1	CR4115	Angled punched plate for 4 x RJ45 (37 mm x 22 mm cut-outs)
1	CR4106	2 x LJ2 accessory plate (50 mm fixing centres)
1	CR4108	4 x BNC connector plate
1	CR4112	4 x Data / telecoms plate (37 mm x 22 mm cut-outs)
1	CR4113	6 x Data / telecoms plate (37 mm x 22 mm cut-outs)
1	CR4110	75 mm plate for 2 x 50 mm x 50 mm Euromod
1	CR4200	75 mm plate for 3 x 45 mm x 45 mm Arteor modules

Pack	Cat. Nos.	Ancillary items for service outlet boxes
1	CR0001	Floor tile cut-out template – 2 compartment
1	CR0003	Floor tile cut-out template – 3 / 4 compartment
10	CR0000	Cable outlet flap
10	CR0010	Cable routers
50	CR0011	Screws for accessory plates
1	CR0012	Pack of 5 keys for use with lockable floor boxes
1	CR0021	Plastic lid and trim for 2 compartment floor box
1	CR0022	Plastic lid and trim for 3 / 4 compartment floor box
1	CR0023	Lockable lid assembly for 2 compartment floor box
1	CR0024	Lockable lid assembly for 3 / 4 compartment floor box
1	CR0005	Mounting frame for vinyl floor. For 2 compartment box Replaces mounting frame attached to base
1	CR0006	Mounting frame for vinyl floor. For 3 / 4 compartment box. Replaces mounting frame attached to base
10	CR0007	Floor box lid handle
1	CR0020	Metal lid and trim - replacement for 3 and 4 compartment boxes - powder coated grey

Electrak tap-offs p. 10-14, 16-17