

Hypra® IP 44 - LV 32 A

metal and plastic plugs and sockets



Technical information and dimensions **p. 93-95**
Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS EN 60309-2, IEC 60309-1 and IEC 60309-2
IP 44 according to BS EN 60529 and IEC 60529
IK 09 plastic
IK 10 metal according to BS EN 62262 and IEC 62262
Self-extinguishing : 850 °C for insulated parts
650 °C for housing - conforms to BS EN 60695-2-10 and IEC 60695-2-10
Temp. rating : -50 °C to +100 °C
Nickel plated brass contacts

Pack	Cat. Nos.		Panel mounting sockets 32 A
	Metal	Modular	200 to 250 V~
1	0527 32	0527 18	2 P + ⊥
1	0527 33	0527 19	3 P + ⊥
			380 to 415 V~
1	0529 33	0529 19	3 P + ⊥
1	0529 34	0529 20	3 P + N + ⊥

Pack	Cat. Nos.	Mobile sockets 32 A
	Plastic	200 to 250 V~
1	0527 82	2 P + ⊥
1	0527 83	3 P + ⊥
		380 to 415 V~
1	0529 83	3 P + ⊥
1	0529 84	3 P + N + ⊥

Pack	Cat. Nos.	Straight plugs 32 A
	Plastic	200 to 250 V~
1	0527 42	2 P + ⊥
1	0527 43	3 P + ⊥
		380 to 415 V~
1	0529 43	3 P + ⊥
1	0529 44	3 P + N + ⊥

Pack	Cat. Nos.	Panel appliance inlets 32 A
	Plastic	200 to 250 V~
1	0528 72	2 P + ⊥
		380 to 415 V~
1	0528 73	3 P + ⊥
1	0528 74	3 P + N + ⊥

Pack	Cat. Nos.	Back boxes
	Metal	Surface mounting boxes
1	0529 39	For LV 32 A 2 P + ⊥ / 3 P + ⊥ / 3 P + N + ⊥ sockets
	Plastic	Through entry surface mounting boxes
1	0529 90	For LV 32 A 2 P + ⊥ / 3 P + ⊥ / 3 P + N + ⊥ sockets

Pack	Cat. Nos.	Appliance inlet covers
5	0521 27	For LV 32 A 2 P + ⊥ / 3 P + ⊥ appliance inlets
5	0527 99	For LV 32 A 3 P + N + ⊥ appliance inlets

Hypra® IP 44 - LV 63 A

metal and plastic plugs and sockets



Technical information and dimensions **p. 93-95**
Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS EN 60309-2, IEC 60309-1 and IEC 60309-2
IP 44 according to BS EN 60529 and IEC 60529
IK 09 plastic
IK 10 metal according to BS EN 62262 and IEC 62262
Self-extinguishing : 850 °C for insulated parts
650 °C for housing - conforms to BS EN 60695-2-10 and IEC 60695-2-10
Temp. rating : -50 °C to +100 °C
Nickel plated brass contacts. 63 A units have a pilot pin

Pack	Cat. Nos.		Panel mounting sockets 63 A
	Metal	Plastic	380 to 415 V~
1	0538 33	0538 23	3 P + ⊥
1	0538 34	0538 24	3 P + N + ⊥

Pack	Cat. Nos.	Surface mounting socket 63 A
	Plastic	380 to 415 V~
1	0537 24	3 P + N + ⊥

Pack	Cat. Nos.	Mobile sockets 63 A
	Plastic	380 to 415 V~
1	0538 83	3 P + ⊥
1	0538 84	3 P + N + ⊥

Pack	Cat. Nos.	Straight plugs 63 A
	Plastic	380 to 415 V~
1	0538 43	3 P + ⊥
1	0538 44	3 P + N + ⊥

Pack	Cat. Nos.	Panel appliance inlets 63 A
	Plastic	380 to 415 V~
1	0537 73	3 P + ⊥
1	0537 74	3 P + N + ⊥

Pack	Cat. Nos.	Appliance inlet cover
5	0536 99	For LV 63 A 3 P + ⊥ / 3 P + N + ⊥ appliance inlets