

# Hypra® IP 44 combination units - LV 16/32/63 A

plastic surface mounting



Technical information and dimensions **p. 120-122**  
 Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS EN 60309-2 and IEC 60309-1, IEC 60309-2  
 IP 44 conforms to BS EN 60529 and IEC 60529  
 IK 09 conforms to BS EN 62262 and IEC 62262  
 Temp. rating : -15 °C to +40 °C\*  
 RAL 7022

Pack	Cat. Nos.		Single socket units with switch
	16 A	32 A	Double mechanical interlock
1	0592 00		<b>100 to 130 V~</b> 2 P + ⊥
1	0592 03	0592 43	<b>200 to 250 V~</b> 2 P + ⊥
1	0592 09	0592 49	<b>380 to 415 V~</b> 3 P + ⊥
1	0592 16	0592 56	3 P + N + ⊥
	63 A		<b>380 to 415 V~</b> 3 P + ⊥
1	0592 34		3 P + N + ⊥
1	0592 35		3 P + N + ⊥

Pack	Cat. Nos.		Single socket units protected by 30 mA RCBO
	16 A	32 A	Transparent plastic hinged viewing window Supplied complete with 16/32 A 30 mA RCBO With 5 module DIN rail
1	0592 07	0592 47	<b>200 to 250 V~</b> with RCBO 2 P + ⊥
1	0592 14		<b>380 to 415 V~</b> with RCBO 3 P + ⊥
1	0592 19	0592 59	3 P + N + ⊥

Pack	Cat. Nos.		Single socket units with switch and protected by 30 mA RCBO
	16 A	32 A	Transparent plastic hinged viewing window Supplied complete with 16/32 A 30 mA RCBO With 6 module DIN rail
1	0596 01	0596 05	<b>200 to 250 V~</b> with RCBO 2 P + ⊥
1	0596 02	0596 07	<b>380 to 415 V~</b> with RCBO 3 P + ⊥
1	0596 03	0596 08	3 P + N + ⊥

Pack	Cat. Nos.		Single socket units with switch and protected by RCD
	63 A		Transparent plastic hinged viewing window Supplied complete with RCD With 6 module DIN rail
1	0592 83		<b>380 to 415 V~</b> 3 P + ⊥ with MCB + RCD add-on module
1	0592 84		3 P + N + ⊥ with RCD

Pack	Cat. Nos.		Prisinter single socket units protected by 30 mA RCBO
	16 A	32 A	Transparent plastic hinged viewing window Cable glands are not supplied (ISO) With 6 module DIN rail
1	0592 24		<b>IP 44 plug inserted</b> <b>IP 55 lid closed or connected to an IP 66/67-55 angled plug</b> <b>200 to 250 V~</b> 2 P + ⊥
1		0592 28	<b>380 to 415 V~</b> 3 P + ⊥
1		0592 29	3 P + N + ⊥

1 : Units with RCBO and some MCB protection devices have temperature ratings of -5 °C to +40 °C  
 Switch only units and some MCBs have increased ratings - please contact us on +44 (0) 345 605 4333

Hypra IP 44 straight plugs **p. 90**



Hypra IP 66/67-55 angled and straight plugs **p. 96**

