



# Swifts® cable ladder ancillary items (continued)

Topaz, Sapphire and Emerald



Dimensions and technical information (p. 84-94)

Pack	Cat. Nos.	Ancillary items (continued)	Pack	Cat. Nos.	Ancillary items (continued)
		<b>Straight dividers – 3-0 m</b> Supplied with fasteners For technical information, see p. 84			<b>Dropout plate</b> Supplied with fasteners Use to provide local support for cables as they exit a cable ladder run between rungs For technical information, see p. 87
1	ZDV F	Medium duty (Topaz)	1	DO W F	All ladder types
1	PDV F	Heavy duty (Sapphire)			<b>Rail-to-rail dropout brackets</b> Supplied in pairs with fasteners Use to attach a vertical run of ladder or tray beneath a horizontal main ladder run For technical information, see p. 88
1	EDV F	Extra heavy duty (Emerald)	1	M F	For ladder to ladder connection  or Tray to ladder connection
		<b>Curved dividers – 1-0 m</b> Supplied with fasteners Drill on site to suit rung position For technical information, see p. 84			<b>Tee brackets</b> Supplied in pairs with fasteners Use to create a branch of a straight ladder run For technical information, see p. 89
1	ZCUR F	Medium duty (Topaz)	1	ZTB F	Medium duty (Topaz)
1	PCUR F	Heavy duty (Sapphire)	1	PTB F	Heavy duty (Sapphire)
1	ECUR F	Extra heavy duty (Emerald)	1	ETB F	Extra heavy duty (Emerald)
		<b>Vertical hinged connectors</b> Supplied in sets comprising four plates and fasteners Use with straight lengths to form risers or solve minor misalignment problems on site When used with tee bracket, vertical hinged connectors can offset tee branch For technical information, see p. 42			<b>Stop ends</b> Supplied singly with fasteners. Use to terminate a ladder run, or to fix the end of a run to a vertical surface For technical information, see p. 94
1	ZV F	Medium duty (Topaz)	1	ZSW F	Medium duty (Topaz)
1	PV F	Heavy duty (Sapphire)	1	PSW F	Heavy duty (Sapphire)
1	EV F	Extra heavy duty (Emerald)	1	ESW F	Extra heavy duty (Emerald)
		<b>Articulated risers</b> Set comprises three ladder sections and the necessary vertical hinged connectors with fasteners Use to form risers or solve most misalignment problems on site For technical information, see p. 85-86			
1	ZAR W F	Medium duty (Topaz)			
1	PAR W F	Heavy duty (Sapphire)			
1	EAR W F	Extra heavy duty (Emerald)			

Key : selecting ancillary items. Replace the letters shown in red with your choice from the following options :

W = Widths (mm) : 150, 300, 450, 600, 750, 900  
 F = Finish : G (hot dip galvanised after manufacture),  
 D (deep galvanised) S (stainless steel), E (powder coated)