




























Swiftrack channel support system

framework brackets

90° brackets					
					
Cat. No. SB500	Cat. No. SB501	Cat. No. SB502	Cat. No. SB503	Cat. No. SB504	
					
Cat. No. SB505	Cat. No. SB550	Cat. No. SB551	Cat. No. SB552	Cat. No. SB556	
Square and splice plates					
<p>Square plates</p>  <p>Cat. Nos. SB506 06 SB506 08 SB506 10 SB506 12</p> <p>Hole size M6 M8 M10 M12</p>	<p>Splice plate¹</p>  <p>Cat. No. SB507</p>	<p>Splice plate¹</p>  <p>Cat. No. SB508</p>	<p>Splice plate¹</p>  <p>Cat. No. SB509</p>	<p>Splice plate¹</p>  <p>Cat. No. SB510</p>	
Z brackets			U brackets		
					
Cat. No. SB511	Cat. No. SB513	Cat. No. SB514	Cat. No. SB515		
Angle brackets					
	<p>Obtuse angle brackets</p> <p>Cat. Nos. Angle</p> <p>SB520 15°</p> <p>SB524 45°</p> <p>SB526 60°</p> <p>SB528 75°</p>		<p>Acute angle brackets</p> <p>Cat. Nos. Angle</p> <p>SB532 45°</p> <p>SB534 60°</p> <p>SB536 75°</p>		
T plates and brackets					
					
Cat. No. SB554	Cat. No. SB555	Cat. No. SB603	Cat. No. SB603+	Cat. No. SB606³	Cat. No. SB607³

1 : Splice plates – holes spaced at 45 mm centres

2 : Hole on one side of bracket only

3 : SB606 and SB607 are not available in S (stainless steel) finish

Swiftrack channel support system

framework brackets (continued)

Joining brackets and channels			Base plates		
Channel joining bracket Cat. No. SB518	Joining channel for SC200 channel Cat. No. SB650	Joining channel for SC400 channel Cat. No. SB651	Single channel base plate Cat. No. SB704	Double channel base plate Cat. No. SB705	
L brackets			Wing brackets		
L bracket Cat. No. SB600	Right hand L corner bracket Cat. No. SB601 ²	Left hand L corner bracket Cat. No. SB602 ²	2 lug wing bracket Cat. No. SB700	3 lug wing bracket Cat. No. SB701	Angled wing bracket Cat. No. SB707 ²
Gusseted brackets			Shelf brackets		
Single channel gusseted bracket Cat. No. SB702	Double channel gusseted bracket Cat. No. SB706	Shelf brackets Cat. No. SB703			
Beam, window beam and toe beam clamps					
Beam clamp³ Cat. No. SC850	Beam clamp³ Cat. No. SC851	Window beam clamp³ Cat. No. SC852/21	Window beam clamp³ Cat. No. SC852/41	Beam clamp³ Cat. No. SC852/82	
Beam clamp³ Cat. No. SC853	Beam clamp³ Cat. No. SC854	Toe beam clamp³ Cat. No. SC856 ⁴	Beam clamp³ Cat. No. ZC1 ⁵	Beam clamp³ Cat. No. FL2 ⁵	Beam clamp³ Cat. No. SC855
Pipe clamps ⁶			Channel accessories		
 Cat. Nos. SP960 10-14 SP964 17-22 SP965 22-26 SP968 25-35 SP969 32-42 SP972 42-59 SP973 54-65	 Cat. Nos. SP975 62-71 SP976 73-83	Channel end caps⁷ Cat. Nos. SC950B SC950W	Channel end caps⁸ Cat. Nos. SC951B SC951W	Closure strips Cat. Nos. SC952 SC953	
-			-		

1 : Indicates inside dimensions 2 : SB601, SB602 and SB707 are not available in S (stainless steel) finish
 3 : Beam clamps are supplied with nuts, bolts, cone point screws and U bolts where shown 4 : Requires 2 setscrews and channel nuts for fixing (not included)
 5 : Stainless steel finish is not available 6 : All pipe clamps are available in pre-galvanised and stainless steel finishes
 7 : For SC400, SC401 and SC403 channels 8 : For SC200, SC201 and SC203 channels