

## access floor pre-wired service outlet boxes

### 3 and 4 compartment



CR100



CR122

 Selection chart **p. 28-29**  
Dimensions and technical information **p. 33**

Electrak floor boxes can be supplied pre-wired to powertrack tap-offs with any variation of sockets, tap-offs, depth or other configuration


Pack	Cat. Nos.	<b>3 compartment pre-wired boxes with 1 x TSSO</b>
		<b>100 mm compartment widths</b>
		Single base – 85 mm depth, pre-wired with :
1	CR100	3 m Electrak 24 standard tap-off Cat. No. DP1332
1	CR101	5 m Electrak 24 standard tap-off Cat. No. DP1532
1	CR110	3 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2332
1	CR111	5 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2532
1	CR104	3 m Electrak 28 auxiliary earth tap-off Cat. No. YP5332
1	CR105	5 m Electrak 28 auxiliary earth tap-off Cat. No. YP5532

Pack	Cat. Nos.	<b>3 compartment pre-wired boxes with 2 x TSSO</b>
		<b>100 mm compartment widths</b>
		Single base – 85 mm depth, pre-wired with :
1	CR102	3 m Electrak 24 standard tap-off Cat. No. DP1332
1	CR103	5 m Electrak 24 standard tap-off Cat. No. DP1532
1	CR112	3 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2332
1	CR113	5 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2532
1	CR106	3 m Electrak 28 auxiliary earth tap-off Cat. No. YP5332
1	CR107	5 m Electrak 28 auxiliary earth tap-off Cat. No. YP5532

Pack	Cat. Nos.	<b>4 compartment pre-wired boxes with 1 x TSSO</b>
		<b>75 mm compartment widths</b>
		Single base – 85 mm depth, pre-wired with :
1	CR120	3 m Electrak 24 standard tap-off Cat. No. DP1332
1	CR121	5 m Electrak 24 standard tap-off Cat. No. DP1532
1	CR130	3 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2332
1	CR131	5 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2532
1	CR124	3 m Electrak 28 auxiliary earth tap-off Cat. No. YP5332
1	CR125	5 m Electrak 28 auxiliary earth tap-off Cat. No. YP5532

Pack	Cat. Nos.	<b>4 compartment pre-wired boxes with 2 x TSSO</b>
		<b>75 mm compartment widths</b>
		Single base – 85 mm depth, pre-wired with :
1	CR122	3 m Electrak 24 standard tap-off Cat. No. DP1332
1	CR123	5 m Electrak 24 standard tap-off Cat. No. DP1532
1	CR132	3 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2332
1	CR133	5 m Electrak 25 low noise / clean earth tap-off Cat. No. JP2532
1	CR126	3 m Electrak 28 auxiliary earth tap-off Cat. No. YP5332
1	CR127	5 m Electrak 28 auxiliary earth tap-off Cat. No. YP5532

Pre-wired floor boxes can be supplied with RCD 30 mA rather than standard sockets. Add an **R** to the end of the part numbers for a RCD 30 mA version or an **RS** for a RCD 30 mA switched socket version.  
TSSO = twin switched socket outlet  
For example CR100**R** is a 3 compartment floor box with a twin RCD socket and a DP1332 tap-off

 Also available :  
- pre-wired boxes with fused tap-offs  
- shallow or deep versions  
- separate compartment bases  
**contact us on +44 (0) 370 608 9020**



NOTE : Please consult us for different plate options on +44 (0) 370 608 9020. Photos are only illustrative.