

Arteor™ USB charging sockets



Support frames and surround plates selection charts **p. 30, 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	USB Type-A charging sockets
		For recharging portable devices Conform to IEC 62684-2011-01 Consumption in passive mode < 0.6 W 2P + E tap-off connection via 2 x 2.5 mm ² screw terminals Supplied without cord
		Double USB sockets - 5 V - 2.4 A - 12 W For fast charging smartphones and tablets 2 modules
5	5720 78	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5725 78	
1	5710 76	
1	5700 76	
		Single USB sockets - 5 V - 1.5 A - 7.5 W For smartphone or powerbank 1 module
10	5720 71	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5725 71	
10	5710 75	
10	5700 75	

Pack	Cat. Nos.	Micro USB charging dock - 2.4 A
		For recharging portable devices Conform to IEC 62684-2011-01 Consumption in passive mode < 0.6 W 2P + E tap-off connection via 2 x 2.5 mm ² screw terminals Cordless Micro USB cradle for charging a smartphone Equipped with a lateral USB port for a second device Clamp holder for smartphone with a non slip coating and antiscratch Smartphone screen remains visible during charging Possible to charge an iPhone by using the micro USB lightning adaptor iPhone is a registered Apple brand The accessory is not supplied with the product
1	5720 79	<ul style="list-style-type: none"> ○ White ● Magnesium
1	5725 79	

Pack	Cat. Nos.	USB Type-C charging sockets
		Used for charging portable devices without a mobile charger with USB Type-C plug Standby consumption < 0.06 W Conform to IEC 62684-2011-01 Supplied without cord
		1 USB Type-A + 1 USB Type-C - 230 V - 5 V = - 3 A - 15 W 2 modules
1	5720 77	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5725 77	
1	5710 77	
1	5700 77	
		2 USB Type-C - 230 V - 5 V = - 3 A - 15 W 2 modules
1	5720 72	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5725 72	
1	5710 78	
1	5700 78	
		1 USB Type-C - 230 V - 5 V = - 1.5 A - 7.5 W 1 module
10	5724 84	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
10	5733 94	
10	5710 79	
10	5700 79	