

CX³ push-buttons, control switches and LED indicators **N**



Dimensions p. 47

Pack	Cat. Nos.	Push buttons and control switches	
		Conform to IEC 60669-1 Nominal rating 20 A - 250 V \sim Compatible with fluorescent lamps (20 AX) Accept prong-type supply busbars	
		Single function push buttons	
10	4129 08	1 NO	Connection: Number of modules: 1
10	4129 09	1 NC	Connection: Number of modules: 1
		Dual functions push buttons without indicator	
10	4129 16	1 NO (green push button) + 1 NC (red push-button)	Connection: Number of modules: 1
		Single function control switches	
10	4129 10	2 NO	Connection: Number of modules: 1
10	4129 11	1 NO + NC	Connection: Number of modules: 1
		Dual functions control switches with indicator	
10	4129 12	1 NO + green LED indicator 12/48 V \sim / \equiv	Connection: Number of modules: 1
10	4129 13	1 NC + red LED indicator 12/48 V \sim / \equiv	Connection: Number of modules: 1
10	4129 14	1 NO + green LED indicator 110/400 V \sim	Connection: Number of modules: 1
10	4129 15	1 NC + red LED indicator 110/400 V \sim	Connection: Number of modules: 1

Pack	Cat. Nos.	LED indicators	
		Equipped with non replaceable LED lamps LED life: 100 000 h LED consumption: 0.17 W under 230 V \sim / 0.11 W under 24 V \sim Conform to IEC 60947-5-1 Accept prong-type supply busbars	
		Single - 12/48 V\sim/\equiv	
10	4129 21	● Green	Connection: Number of modules: 1
10	4129 22	● Red	
10	4129 23	● Yellow	
10	4129 24	● Blue	
10	4129 25	○ White	
10	4129 25	○ White	
		Single - 110/400 V\sim	
10	4129 26	● Green	Connection: Number of modules: 1
10	4129 27	● Red	
10	4129 28	● Yellow	
10	4129 29	● Blue	
10	4129 30	○ White	
		Double - 110/400 V\sim	
10	4129 31	● ● Green/Red	Connection: Number of modules: 1
		Triple - 230/400 V\sim	
10	4129 32	○ ○ ○ White	Connection: Number of modules: 1
10	4129 33	● ● ● Red	
10	4129 34	● ● ● Red/Yellow/Green	
10	4129 35	● ● ● Red/Yellow/Blue	
		TX³ LED indicators - 230 V\sim	
		Equipped with non replaceable LED lamps	
		Single	
12	6040 77	● Green	Connection: Number of modules: 1
12	6040 78	● Red	
12	6040 79	● Orange	

Changeover switches p. 31

