



7300 10



7301 10



7300 18



7300 19



7301 20



7300 23



7300 29

Technical information p. 56

Front plates : white thermoset
Terminal screws captive and backed off ready for cabling
Supplied with faceplate screw caps

Pack	Cat. Nos.	Double pole switches 20 A - 250 V ¹
		Conform to BS EN 60669-1 : 2000 Options available as standard with red 'power on' LED indicator LED 'power on' upgrade pack also available (p. 54) Use cord outlet accessory box Cat. No. 7300 53 for flush to wall external cord connection (p. 54) Flush mounting back box : min. 25 mm deep Nominal plate dimensions : 86 x 86 mm
10	7300 10	20 A DP
10	7301 10	20 A DP marked 'WATER HEATER'
10	7300 14	20 A DP with cord outlet
10	7301 14	20 A DP with cord outlet marked 'WATER HEATER'
10	7300 16	20 A DP with cord outlet + red LED power indicator
10	7301 16	20 A DP with cord outlet marked 'WATER HEATER' + red LED power indicator
10	7300 12	20 A DP + red LED power indicator
10	7301 12	20 A DP marked 'WATER HEATER' + red LED power indicator
10	7300 18	20 A sink/bath dual switch + red LED power indicator

Pack	Cat. Nos.	Cable outlet 20 A - 250 V ¹
10	7300 19	20 A – with terminal block and outlet gland

Red power indicator LED pack p. 54

¹ : Range of engraving available on most products, see table on p. 57

Flush and surface mounting back boxes p. 55



Pack	Cat. Nos.	Double pole switches 45 A - 250 V ¹
		Conform to BS EN 60669-1 : 2000 Options available as standard with red 'power on' LED indicator LED 'power on' upgrade pack also available (p. 54) Flush mounting back box : min. 48 mm deep Nominal plate dimensions : 146 x 86 mm
5	7300 20	45 A DP
5	7301 20	45 A DP with red rocker marked 'COOKER'
5	7300 21	45 A DP + red LED power indicator
		Nominal plate dimensions : 86 x 86 mm
10	7300 22	45 A DP
10	7301 22	45 A DP with red rocker marked 'COOKER'
10	7300 23	45 A DP + red LED power indicator

Pack	Cat. Nos.	Cooker control units 45 A - 250 V ¹
		Conform to BS 4177 : 1992 Options available as standard with red 'power on' LED indicator LED 'power on' upgrade pack also available (p. 54) 45 A - 250 V ¹ double pole switch with 13 A - 250 V ¹ double pole switched socket outlet Flush mounting back box : min. 48 mm deep Nominal plate dimensions : 86 x 146 mm
5	7300 28	DP with DP switched socket
5	7300 29	DP with DP switched socket + red LED power indicator

Pack	Cat. Nos.	Cable outlet 45 A - 250 V ¹
5	7300 26	45 A – with terminal block