



7300 95



7300 96




7300 99

Arteor modules **p. 9-29**

7301 58



7301 91



7301 94



7354 91

Complete range of grid front plates and modules **p. 80-85**

Technical information p. 56

Grid selection charts p. 84-85
Grid modules p. 80-81
Arteor modules p. 9-29

Pack	Cat. Nos.	Accessories
Blanking plates		
10	7300 95	1 gang - 86 x 86 mm
10	7300 96	2 gang - 86 x 146 mm
LED packs		
Relevant Synergy functions are designed to accept LED packs for fitting at time of installation or retrospectively by a qualified person Compatible with fluorescent loads		
10	7301 58	Electronic LED locator pack – green diodes : max. current 0.2 mA provides illumination to locate function such as switches in low light
10	7300 58	Electronic LED power indicator pack – red diodes : nominal current 2 mA provides indication of 'power on' condition in such functions as sockets and control switches
Outlet plate - VDI/low voltage		
10	7300 52	1 gang - 86 x 86 mm with cable clamp and outlet gland
Contrast frames		
Aid Part M compliance when using Synergy White wiring accessories		
10	8218 46	1 gang contrast frame
10	8218 47	2 gang contrast frame
Accessory frames		
10	7300 53	1 gang - 86 x 86 x 11 mm with bottom cord outlet For flush to wall external cord connection suitable for use with 13 A and 20 A control switches and other relevant 86 x 86 mm functions Integral cord grip
10	7301 95	1 gang - 86 x 86 x 7 mm spacer frame
5	7301 96	2 gang - 86 x 146 x 7 mm spacer frame
Spare screw cap covers		
10	7301 53	Pack of 50 caps to cover mounting screws

Pack	Cat. Nos.	Euro module front plates
Suitable for use with standard 25 x 50 mm Euro data module inserts		
10	7300 99	1 gang - 86 x 86 mm 2 modules - aperture size 50 x 50 mm
10	7301 00	2 gang - 86 x 146 mm 4 modules - aperture size 50 x 100 mm
Carrier plates for Arteor, Nuvo or Vantage modules (square)		
No additional support frame required Enable a Synergy installation to benefit from additional functionality, such as international sockets and to match audio and lighting systems with wiring accessories		
10	7300 91	1 gang - 86 x 86 mm 1 module
10	7300 92	1 gang - 86 x 86 mm 2 modules
10	7300 93	2 gang - 86 x 146 mm 3 modules
10	7300 94	2 gang - 86 x 146 mm 4 modules
1 and 2 gang front plates for grid modules		
Must be used with support frames, see below		
10	7301 91	1 gang - 86 x 86 mm 1 small aperture module
10	7301 92	1 gang - 86 x 86 mm 2 small aperture modules
10	7301 93	2 gang - 86 x 146 mm 3 small aperture modules
10	7301 94	2 gang - 86 x 146 mm 4 small aperture modules
1, 2 and 3 gang support frames for grid modules		
10	7354 90	1 gang 1 module
10	7354 91	1 gang 2 modules
10	7354 92	2 gang 3/4 modules
10	7354 93	3 gang 6 modules