

# Synergy® Authentic

## plates and support frames



8330 93

Polished stainless steel front plates : electroplated stainless steel plate with trivalent chrome for mirror finish  
Terminal screws captive and backed off ready for cabling



8331 91



7354 90



7354 91

Pack	Cat. Nos.	Euro module front plates
		Suitable for use with 25 x 50 mm Euro data module inserts
		<b>1 gang - 2 modules</b>
		Nominal plate dimensions : 86 x 86 mm
1	8211 99	● Brushed stainless steel
1	8212 99	● Polished stainless steel
1	8213 99	● Gold
		<b>2 gang - 4 modules</b>
		Nominal plate dimensions : 86 x 146 mm
1	8211 00	● Brushed stainless steel
1	8212 00	● Polished stainless steel
1	8213 00	● Gold

Pack	Cat. Nos.	Carrier plates for Arteor, Nuvo and Vantage modules (square)
		No additional support required Enables a Synergy installation to benefit from additional functionality such as international sockets and to match audio and lighting systems with the wiring accessories
		<b>1 gang - 1 module</b>
		Nominal plate dimensions : 86 x 86 mm
1	8330 91	● Brushed stainless steel
1	8332 91	● Polished stainless steel
1	8334 91	● Gold
		<b>1 gang - 2 modules</b>
		Nominal plate dimensions : 86 x 86 mm
1	8330 92	● Brushed stainless steel
1	8332 92	● Polished stainless steel
1	8334 92	● Gold
		<b>2 gang - 3 modules</b>
		Nominal plate dimensions : 86 x 146 mm
1	8330 93	● Brushed stainless steel
1	8332 93	● Polished stainless steel
1	8334 93	● Gold
		<b>2 gang - 4 modules</b>
		Nominal plate dimensions : 86 x 146 mm
1	8330 94	● Brushed stainless steel
1	8332 94	● Polished stainless steel
1	8334 94	● Gold

Grid selection charts **p. 84-85**  
Grid modules **p. 80-81**  
Arteor modules **p. 9-29**

Pack	Cat. Nos.	1 and 2 gang front plates for grid modules
		For support frames, see below
		<b>1 gang - 1 small aperture module</b>
		Nominal dimensions : 86 x 86 mm
1	8331 91	● Brushed stainless steel
1	8333 91	● Polished stainless steel
1	8335 91	● Gold
		<b>1 gang - 2 small aperture modules</b>
		Nominal dimensions : 86 x 86 mm
1	8331 92	● Brushed stainless steel
1	8333 92	● Polished stainless steel
1	8335 92	● Gold
		<b>2 gang - 3 small aperture modules</b>
		Nominal dimensions : 86 x 146 mm
1	8331 93	● Brushed stainless steel
1	8333 93	● Polished stainless steel
1	8335 93	● Gold
		<b>2 gang - 4 small aperture modules</b>
		Nominal dimensions : 86 x 146 mm
1	8331 94	● Brushed stainless steel
1	8333 94	● Polished stainless steel
1	8335 94	● Gold

Pack	Cat. Nos.	1, 2 and 3 gang support frames for grid modules
10	7354 90	1 gang 1 module
10	7354 91	1 gang 2 modules
10	7354 92	2 gang 3/4 modules
10	7354 93	3 gang 6 modules

Arteor modules  
**p. 9-29**



Complete range of grid front plates and modules  
**p. 80-85**

