

# Intermod under-desk modules



IPP403



IPP408



IPP405



IPP452

Intermod complies with the relevant parts of BS 5733, and BS 1363 Part 2, where appropriate. Manufactured in an approved ISO 9001 facility in the UK. Intermod is a new system which is fully compatible with Intersoc. The two systems can be mixed to provide almost limitless combinations of power and data. When Intermod is being used without Intersoc socket modules, select the feed, protection, and accessories from the Intersoc range. Modules with data must always be fitted as the last module in the Intersoc/Intermod daisy chain.

**Intermod can be manufactured with different combinations of power and data. For details contact us on +44 (0) 370 608 9020**

Pack	Cat. Nos.	Intermod 4 module standard units
<b>Standard power only versions</b>		
1	IPP401	4 x Schuko sockets - shuttered
1	IPP402	4 x Swiss sockets - shuttered, child safety
1	IPP403	4 x Chinese sockets - shuttered, child safety
1	IPP404	4 x Australian sockets - shuttered, child safety
1	IPP405	4 x French sockets - shuttered, child safety
1	IPP406	4 x Israeli sockets - shuttered, child safety
1	IPP407	4 x S. African sockets - shuttered, child safety
1	IPP408	4 x American sockets <sup>1</sup>
1	IPP409	4 x Indian sockets
1	IPP410	4 x Universal sockets <sup>2</sup>
<b>Standard mixed power only versions</b>		
1	IPP450	2 x BS and 2 x Schuko sockets
1	IPP451	2 x BS and 2 x French sockets
1	IPP475	2 x BS, 1 x Schuko and 1 x French sockets
1	IPP452	2 x AUS and 2 x Chinese sockets
1	IPP453	2 x AUS and 2 x universal sockets <sup>2</sup>
<b>Standard mixed power and data versions<sup>3</sup></b>		
1	IMP211D02	2 x BS sockets, 1 x USB charging outlet with 1 x Type A and 1 x Type C 3 A, 2 x RJ45 outlets
1	IMP211D01	2 x BS sockets, 1 x USB charging outlet with 2 x Type A 3 A, 2 x RJ45 outlets
1	IMP211D03	2 x BS sockets, 1 x HDMI outlet, 1 x USB charging outlet with 1 x Type A and 1 Type C 3 A, 1 x RJ45 outlet
1	IMP251D04	1 x BS socket and 1 x Schuko socket, 1 x USB charging outlet with 1 x Type A and 1 x Type C 3 A, 2 x RJ45 outlets
1	IMP251D02	1 x BS socket and 1 x French socket, 1 x USB charging outlet with 1 x Type A and 1 Type C 3 A, 2 x RJ45 outlets
1	IMP210D01 <sup>1</sup>	2 x universal sockets, 1 x USB charging outlet with 2 x Type A 3 A, 2 x RJ45 outlets
1	IMP210D02 <sup>2</sup>	2 x universal sockets, 1 x USB charging outlet with 1 x Type A and 1 x Type C 3 A, 2 x RJ45 outlets
<b>Data only version<sup>3</sup></b>		
1	IDD51	2 x USB Types A and C outlets 3 A, 1 x HDMI outlet, 1 x BNC outlet, 1 x BT Sec outlet, 1 x RJ45 outlet


<b>Other feed units</b>		
<b>American versions</b>		
For feed units other than American versions, see p. 5		
1	IAB002US	120 V AC with 2 m 1.5 mm <sup>2</sup> cable with US plug
1	IAB003US	120 V AC with 3 m 1.5 mm <sup>2</sup> cable with US plug

1 : Must be used with US type feed units Cat. Nos. IAB002US or IAB003US  
 2 : Not for use in UK and Europe, please consult us for application suitability on +44 (0) 370 608 9020  
 3 : Modules with data must be fitted as last module on the Intersoc/Intermod daisy chain

## Under-desk dimensions (mm) and module options


### Example socket options

For more information on socket and non-power options contact us +44 (0) 370 608 9020



### Under-desk dimensions

4 socket module



Complies with BS 5733 and relevant parts of BS 1363-2. Manufactured within an approved ISO 9001 and ISO 14001 facility

### Electrical test data

Rated current	up to 32 A
Rated voltage	250 V ~
Frequency	50 Hz

All dimensions (mm) are nominal