

## Arteor™ dimmers

square version



Support frames and surround plates selection charts **p. 30, 32-35**  
Load selection charts **p. 14**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)


### Pack Cat. Nos. Leading edge dimmers

Pack	Cat. Nos.	Leading edge dimmers
		Without neutral, 2 wires
		<b>Rotary dimmer - 400 W</b>
1	5722 13	○ White - 2 modules
1	5727 13	● Magnesium - 2 modules
1	5700 53	● Champagne - 2 modules
1	5710 53	● Soft Alu - 2 modules

Pack	Cat. Nos.	Universal dimmers
		Without neutral, 2 wires
		Push button dimmer for all types of lamp :
		- Dimmable LEDs : 75 W
		- Dimmable compact fluorescent lamps : 75 W
		- Halogen with transformer : 400 VA
		- Fluorescent tube : 200 VA
		- Halogen 230 V and incandescent : 400 W
		Can be associated with one or several push buttons without LED, for ON/OFF or dimming control
		Lights come on at the same lighting level as when they were switched off
1	5722 39	○ White - 2 modules
1	5727 39	● Magnesium - 2 modules
1	5729 37	● Champagne - 2 modules
1	5729 36	● Soft Alu - 2 modules

Pack	Cat. Nos.	Dimmers 1-10 V
		Push button dimmer for ballasts 1-10 V
1	5722 38	○ White - 2 modules
1	5727 38	● Magnesium - 2 modules
1	5729 39	● Champagne - 2 modules
1	5729 38	● Soft Alu - 2 modules

Pack	Cat. Nos.	Active power compensator
1	0401 49	Makes 2 wire electronic lighting control units without neutral compatible with all commercially-available loads (LED, compact fluorescent, ELV halogen with ferromagnetic or electronic ballast, 230 V halogen, fluorescent tube, incandescent) Consumption 0-4 W



## Arteor™ dimmers

round version



Support frames and surround plates selection charts **p. 30, 32-35**  
Load selection charts **p. 14**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

### Pack Cat. Nos. Universal dimmers

Pack	Cat. Nos.	Universal dimmers
		Without neutral, 2 wires
		Push button dimmer for all types of lamp :
		- Dimmable LEDs : 75 W
		- Dimmable compact fluorescent lamps : 75 W
		- Halogen with transformer : 400 VA
		- Fluorescent tube : 200 VA
		- Halogen 230 V and incandescent: 400 W
		Can be associated with one or several push buttons without LED, for ON/OFF or dimming control
		Lights come on at the same lighting level as when they were switched off
1	5743 19	○ White - 2 modules
1	5743 39	● Magnesium - 2 modules
1	5743 10	● Soft Alu - 2 modules

Pack	Cat. Nos.	Dimmers 1-10 V
		Push button dimmer for ballasts 1-10 V
1	5743 18	○ White - 2 modules
1	5743 38	● Magnesium - 2 modules