

# Arteor™

## British standard and international socket outlets



Support frames and surround plates selection charts **p. 30, 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	British standard socket outlets	Pack	Cat. Nos.	South African type socket outlets - 16 A	
5	5721 32	<b>Shuttered for child safety</b> Conform to BS 1363 : Part 2 <b>2P + E switched - 15 A</b> Conform to BS 546 3 modules ○ White ● Magnesium ● Champagne ● Soft Alu	5	5721 22	<b>2P + E switched - shuttered for child safety</b> 3 modules ○ White ● Magnesium	
5	5726 32		5	5726 22		
5	5724 28		<b>2P + E - 13 A</b> Conform to BS 1363 : Part 2 ASTA licence 2 modules ○ White ● Magnesium ● Champagne ● Soft Alu	10	5721 03	<b>Italian type socket outlet - 10/16 A</b> <b>2P + E - shuttered for child safety</b> 1 module ○ White ● Magnesium ● Champagne ● Soft Alu
5	5724 27			10	5726 03	
10	5721 11 <sup>1</sup>	<b>2P + E switched - 13 A</b> Conform to BS 1363 : Part 2 ASTA licence 3 modules ○ White ● Magnesium ● Champagne ● Soft Alu	10	5700 36		
10	5726 11 <sup>1</sup>		10	5710 36		
10	5700 38 <sup>1</sup>	<b>2P + E auto-switched - shuttered for child safety - 10 A</b> 2 modules ○ White	10	5721 15	<b>Swiss type socket outlet - 10 A</b> <b>2P + E Type 13 - shuttered for child safety</b> 2 modules	
10	5710 38 <sup>1</sup>		10	5726 14		
5	5721 30		10	5726 15		
5	5726 30		10	5726 02		
5	5724 67	<b>2P + E - 5 A</b> Conform to BS 546 2 modules ○ White ● Magnesium ● Champagne ● Soft Alu	10	5721 14	<b>Australian type socket outlets</b> 2 modules <b>2P + E auto-switched - shuttered for child safety - 10 A</b> ○ White ● Magnesium ● Champagne ● Soft Alu	
5	5724 67		10	5726 14		
5	5700 44		10	5726 15		
5	5710 44		10	5726 02		
10	5721 10	<b>2P + E - shuttered for child safety - 10/15 A</b> ○ White ● Magnesium ● Champagne ● Soft Alu	10	5721 12	<b>Chinese type socket outlets - 10 A</b> <b>2P + E - shuttered for child safety</b> 2 modules ○ White ● Magnesium ● Champagne ● Soft Alu	
10	5726 10		10	5726 12		
10	5710 71		10	5726 07		
10	5700 71		10	5721 07		
10	5721 18	<b>German standard socket outlets - 16 A</b> 2 modules <b>2P + E - shuttered for child safety</b> ○ White ● Magnesium ● Champagne ● Soft Alu ● Red tamper-proof	10	5721 13	<b>French standard socket outlets - 10/16 A</b> <b>2P + E - shuttered for child safety</b> 2 modules ○ White ● Magnesium ● Champagne ● Soft Alu	
10	5726 18		10	5726 13		
10	5710 41		10	5726 08		
10	5700 41		10	5721 08		
10	5724 63	<b>2P + E with cover</b> ○ White ● Magnesium	10	5720 21	<b>2P + E - shuttered for child safety</b> 2 modules ○ White ● Magnesium ● Champagne ● Soft Alu	
10	5721 19		10	5725 21		
10	5726 19	10	5700 21			
10	5710 40	10	5710 21			
10	5721 17	<b>American type socket outlets 15 A - 127 V</b> <b>2P + E</b> 2 modules ○ White ● Magnesium ● Champagne ● Soft Alu	10	5721 17		
10	5726 17		10	5726 17		
10	5700 40		10	5700 40		
10	5710 40		10	5710 40		

<sup>1</sup> : when using two or more Arteor unswitched 13 A sockets (Cat. Nos. 5721 11/5726 11/5700 38/5710 38) next to each other, it is necessary to separate the sockets with a 1 module spacer (Cat. Nos. 5723 41/5728 41/5700 60/5710 60) p. 30.