

# Synergy® Authentic

telephone, data sockets and television sockets



Slim front plate :

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Telephone sockets
		Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm
		<b>Single master</b>
1	8330 50 <sup>1</sup>	● Brushed stainless steel
1	8332 50 <sup>1</sup>	● Polished stainless steel
1	8334 50 <sup>1</sup>	● Gold
		<b>Single secondary</b>
1	8330 51 <sup>1</sup>	● Brushed stainless steel
1	8332 51 <sup>1</sup>	● Polished stainless steel
1	8334 51 <sup>1</sup>	● Gold
		<b>RJ 11/RJ 12 - single</b>
1	8330 54	● Brushed stainless steel
1	8332 54	● Polished stainless steel
1	8334 54	● Gold

Pack	Cat. Nos.	Data sockets CAT. 6
		Rapid cable connection Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm
		<b>RJ 45 - single</b>
1	8330 56	● Brushed stainless steel
1	8332 56	● Polished stainless steel
1	8334 56	● Gold
		<b>RJ 45 - twin</b>
1	8330 57	● Brushed stainless steel
1	8332 57	● Polished stainless steel
1	8334 57	● Gold

1 : Not suitable for use in Republic of Ireland.

Pack	Cat. Nos.	Television sockets
		Flush mounting back box : min. 47 mm deep Screened Nominal plate dimensions : 86 x 86 mm
		<b>TV socket - single male</b>
1	8330 40	● Brushed stainless steel
1	8332 40	● Polished stainless steel
1	8334 40	● Gold
		<b>SAT socket - single 'F' type</b>
1	8330 41	● Brushed stainless steel
1	8332 41	● Polished stainless steel
1	8334 41	● Gold
		<b>TV-R-SAT socket - 'F' type</b>
1	8330 43	● Brushed stainless steel
1	8332 43	● Polished stainless steel
1	8334 43	● Gold

Pack	Cat. Nos.	Quad outlet
		Quad outlet, TV, radio + 2 satellite + TV return with secondary telephone outlet Nominal plate dimensions : 86 x 146 mm
1	8216 63 <sup>1</sup>	● Brushed stainless steel
1	8216 64 <sup>1</sup>	● Polished stainless steel
1	8216 65 <sup>1</sup>	● Gold

Pack	Cat. Nos.	Media plate (monobloc)
		Comprising : <ul style="list-style-type: none"> <li>• 2 x independent satellite feeds</li> <li>• 1 x terrestrial TV socket suitable for analogue and digital signals</li> <li>• 1 x video return</li> <li>• 1 gang x 2 modules Arteor carrier plate with blanks, suitable for Arteor mechanisms (telephone, HDMI, RJ45, RCA)</li> <li>• 2 x Synergy 2 gang switched double pole 13 A sockets</li> </ul> To be used with back box Cat. No. 8204 58 (see below) Nominal plate dimensions : 206 x 267 mm
1	8216 60	● Brushed stainless steel
1	8216 61	● Polished stainless steel
1	8216 62	● Gold

Pack	Cat. Nos.	Back box for media plate
		Dimensions : 194 x 254 x 35 mm With phase barrier Material : grey epoxy coated steel 35 mm deep box
1	8204 58	

1 : Not suitable for use in Republic of Ireland.