

Synergy® Sleek Design

telephone, data sockets and television sockets



Sleek design

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Telephone sockets
		Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm
		Single master
1	8320 50 ¹	● Brushed stainless steel
1	8322 50 ¹	● Polished stainless steel
1	8324 50 ¹	● Gold
		Single secondary
1	8320 51 ¹	● Brushed stainless steel
1	8322 51 ¹	● Polished stainless steel
1	8324 51 ¹	● Gold
		RJ 11 / RJ 12 - single
1	8320 54	● Brushed stainless steel
1	8322 54	● Polished stainless steel
1	8324 54	● Gold
		Data sockets CAT. 6
		Rapid cable connection Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm
		RJ 45 - single
1	8320 56	● Brushed stainless steel
1	8322 56	● Polished stainless steel
1	8324 56	● Gold
		RJ 45 - twin
1	8320 57	● Brushed stainless steel
1	8322 57	● Polished stainless steel
1	8324 57	● Gold

Pack	Cat. Nos.	Television sockets
		Flush mounting back box : min. 35 mm deep Screened Nominal plate dimensions : 86 x 86 mm
		TV sockets - single male
1	8320 40	● Brushed stainless steel
1	8322 40	● Polished stainless steel
1	8324 40	● Gold
		SAT sockets - single 'F' type
1	8320 41	● Brushed stainless steel
1	8322 41	● Polished stainless steel
1	8324 41	● Gold
		TV-R-SAT sockets - 'F' type
1	8320 43	● Brushed stainless steel
1	8322 43	● Polished stainless steel
1	8324 43	● Gold

1 : Not suitable for use in Republic of Ireland.

Synergy® Sleek Design

blanking plates, cord outlets



Sleek design

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Pack	Cat. Nos.	Blanking plates
		1 gang
		Nominal plate dimensions : 86 x 86 mm
1	8320 95	● Brushed stainless steel
1	8322 95	● Polished stainless steel
1	8324 95	● Gold
		2 gang
		Nominal plate dimensions : 86 x 146 mm
1	8320 96	● Brushed stainless steel
1	8322 96	● Polished stainless steel
1	8324 96	● Gold
		Cord outlets
		1 gang
		Nominal plate dimensions : 86 x 86 mm
1	8320 52	● Brushed stainless steel
1	8322 52	● Polished stainless steel
1	8324 52	● Gold