


Datasheet

WP3 LED Weatherproof Batten IP65 - Galaxy with DALI Mains

CAT. NO. 659300GADM, 659303GADM, 659306GADM



Cat. No.		659300GADM	659303GADM	659306GADM
Description		WP3 L6 LED BATTEN DALI GALAXY	WP3 L12 LED BATTEN DALI GALAXY	WP3 L15 LED BATTEN DALI GALAXY
Supply Voltage		230-240 V a.c. 50 Hz		
Operation Mode		Switched Maintained		
Classification C ₀ /C ₉₀		C ₀ /D80, C ₉₀ /D50	C ₀ /D125, C ₉₀ /D80	C ₀ /D160, C ₉₀ /D100
Battery		Li-ion 12.8 V 1.5 Ah		Li-ion 12.8 V 3.3 Ah
Light Source		Selectable LED (3000K/4000K/6500K)		
SDCM (MacAdam Ellipse)		3 (Warm/Natural)		
Flicker-Free		Yes		
Luminous flux (lm) (Mains mode)	Warm	3140	5140	6610
	Cool	3310	5360	6890
	Natural	3260	5350	6870
Power Consumption (W)	Mains only	26	42	54
	Emergency pack	3	3	3
	Total	29	45	57
Luminaire Efficacy at 4000K (lm/W)		114	119	121
Power factor		>0.8	>0.9	
Inrush Current		13.6A	35A	
IP Rating		IP65		
IK Rating		IK08		
Retaining Clips		304 Stainless Steel		
Body Construction		Polycarbonate		
Diffuser		Opal polycarbonate		
Length (mm)		664	1274	1574
Weight (kg)		1.8	2.7	3.3
Compliance		AS/NZS 2293, AS/NZS 60598, AS CISPR 15		
Product Marking		 R-NZ		



WP3 LED Weatherproof Batten IP65 - Galaxy with DALI Mains


CAT. NO. **659300GADM, 659303GADM, 659306GADM**



FEATURES

- Embedded Bluetooth for smart device connectivity.
- Low Power Wide Area Network type of communications utilising the LoRa platform.
- LoRa communication to maximise reliability, coverage and infiltration.
- iSmart™ temperature sensing technology for the LIION battery.
- Electronics designed to lengthen the life of the battery, minimising maintenance costs.
- A premium range of LED weatherproof battens.
- Available in 2 foot, 4 foot or 5 foot lengths.
- Tri-colour LED selection.
- LED Light Source Life:
 - 150,000hrs, L80 B50 at ambient temperature of 25°C.
 - 250,000hrs, L70 B50 at ambient temperature of 25°C.
- CRI > 90
- Environmentally friendly battery.
- 5 Year warranty.
- Designed and Manufactured in Australia.

DIMENSIONS



Legrand - Australia
1300 369 777
www.legrand.com.au
ABN 31 000 102 661

Legrand - New Zealand
0800 476 009
www.legrand.co.nz

Refer to your group buying office, Legrand Sales Representative or Legrand Sales Office for pricing.

Please note: specifications are subject to change without prior notice.



LE14856AB

07/2025