

Datasheet



WP3 LED Weatherproof Batten IP65 - Mains

CAT. NO. 659300MA, 659301MA, 659303MA, 659304MA, 659306MA, 659307MA



Cat. No.		659300MA	659301MA	659303MA	659304MA	659306MA	659307MA
Description		WP3 L6 LED BATTEN MAINS		WP3 L12 LED BATTEN MAINS		WP3 L15 LED BATTEN MAINS	
Supply Voltage		230-240 V a.c. 50 Hz					
Movement Sensor for on/off Operation		N/A	Microwave	N/A	Microwave	N/A	Microwave
Light Source		Selectable LED (3000K/4000K/6500K)					
SDCM (MacAdam Ellipse)		3 (Warm/Natural)					
Flicker-Free		Yes					
Luminous flux (lm) (Mains mode)	Warm	1900/2330/2750/3140		3480/4220/4430/5140		4450/5410/5690/6610	
	Cool	1940/2400/2850/3310		3560/4370/4580/5360		4540/5590/5910/6890	
	Natural	1960/2410/2850/3260		3600/4390/4600/5350		4580/5610/5920/6870	
Power Consumption (W)		15/19/23/26		28/34/36/42		35/43/46/54	
Max. Luminaire Efficacy at 4000K		129				130	
Power factor		>0.8		>0.9			
Inrush Current		15A		20A			
IP Rating		IP65					
IK Rating		IK08					
Retaining Clips		304 Stainless Steel					
Body Construction		Polycarbonate					
Diffuser		Opal polycarbonate					
Length (mm)		664		1274		1574	
Weight (kg)		1.3		2.2		2.8	
Compliance		AS/NZS 60598, AS CISPR 15					
Product Marking							

WP3 LED Weatherproof Batten IP65 - Mains


CAT. NO. **659300MA**, **659301MA**, **659303MA**, **659304MA**, **659306MA**, **659307MA**




FEATURES

- A premium range of LED weatherproof battens.
- Available in 2 foot, 4 foot and 5 foot lengths.
- Tri-colour LED selection.
- Lumen select - 4 brightness settings.
- Ideal replacement for T5 equivalents.
- DALI Lumen control & Motion dimming variant available as well.
- LED Light Source Life:
 - 150,000hrs, L80 B50 at ambient temperature of 25°C.
 - 250,000hrs, L70 B50 at ambient temperature of 25°C.
- CRI > 90
- 5 Year warranty.

DIMENSIONS



ON /OFF SENSOR OPERATION



Legrand - Australia
1300 369 777
www.legrand.com.au
ABN 31 000 102 661

Legrand - New Zealand
0800 476 009
www.legrand.co.nz

Refer to your group buying office, Legrand Sales Representative or Legrand Sales Office for pricing.

Please note: specifications are subject to change without prior notice.

LE14860AB



07/ 2025