


## DUCT MOUNTING KITS, HEAVY DUTY, SUSPENSION KITS, FOR 300 mm DUCT

Part number: TC1279-297KIT/297AKIT/297BKIT

### TC1279-297KIT



### TC1279-297AKIT



Comprises: Part No TC1279-297KIT & 2 x 1/2" UNC Threaded Rods, 1 m long & 8 x 1/2" hex. nuts & 8 washers

### TC1279-297BKIT



Comprises: Part No TC1279-297KIT & 2 x 5/8" UNC Threaded Rods, 300 mm long & 8 x 5/8" hex. nuts & 8 washers

## 1. USE / APPLICATION

The mounting bracket kit (Part No: TC1279-297KIT) is used to attach (300x100 mm) plastic duct (Part No's: TC1279-275 or TC1279-275A (with lid)), to duct mounting ironwork. They allow 300 mm ducting to be fitted to either 1/2" or 5/8" UNC threaded rods, or alternatively M12 and M16 metric threaded rods. This kit consists of: a 300 mm duct mounting bracket (Part No: TC1279-297) with 3 x M12 hex head set screws and nuts and 2 x straight brackets (Part No: TC1279-36). The mounting bracket grips the 300 mm ducting and bolts to the supporting brackets. The straight bracket/s are secured onto either 1/2" or 5/8" UNC threaded rods, or alternatively M12 and M16 metric threaded rods; which are supplied with kits (Part No's: TC1279-297AKIT & TC1279-297BKIT). These kits are both available separately. Typically, the 1/2" dia UNC threaded rods (alternatively M12 threaded rods) are used for suspended mounting from the ceiling; whilst the 5/8" dia UNC threaded rods (alternatively M16 threaded rods) are used for mounting the duct system above racks.

## 2. BENEFITS & FEATURES

- Simple, direct application
- Robust & economical, duct mounting system/s
- Kit (Part No: TC1279-297KIT) Includes: 2 x straight brackets (Part No: TC1279-36), 300 mm duct support bracket, 3 x M12 hex head set screws, nuts & washers
- Kits: (Part No's: TC1279-297AKIT & TC1279-297BKIT) contains: Kit (Part No: TC1279-297KIT) & 2 x threaded rods (as above) & 8 hex nuts & 8 washers. These kits are available separately
- Purchase as individual kits

## 3. TECHNICAL ATTRIBUTES

Dimensions	50 mm (W) x 32 mm (H) x 330 mm (D) [TC1279-297KIT]
Weight	950 grams (TC1279-297KIT) 3.6 kg (TC1279-297AKIT) 2.1 kg (TC1279-297BKIT)
Materials	Mild steel Extensions: Nickel Plated finish Duct Bracket: Powder coat Black Threaded rod, nuts & washers: zinc plated finish