



128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

Céliane™ USB Type-A + USB Type-C charger USB Type-C charger

Cat. No(s): 0 674 65/66



0 674 65



0 674 66


1. USE

For recharging portable devices such as phones, smartphones, tablets, MP3 or MP4 players, loudspeakers, watches, game consoles, powerbanks.

2. RANGE

| USB chargers 5.0 V= / 3.0 A | Cat. No(s) |
|---|------------|
| 1 USB Type-A + 1 USB Type-C (1 output Type-A - 1 output Type-C) | 0 674 65 |
| 1 USB Type-C (2 outputs Type-C) | 0 674 66 |

3. DIMENSIONS (mm)



4. CONNECTION

Type of terminals: with screws Terminal capacity: 2 x 2.5 mm² Stripping length: 6 mm Screwdriver: flat 3.5 mm

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Impact tests: IK 04 Penetration by solid bodies/liquid: IP 40

■ 5.2 Material characteristics

Polycarbonate

Self-extinguishing:

 850° C/30 s for insulating parts holding live parts in place. 650° C/30 s for other insulating components.

5.3 Climate characteristics

Storage temperature: -20° C to $+70^{\circ}$ C Operating temperature: 0° C to $+45^{\circ}$ C

5.4 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

| Nominal input voltage | 100-240 V~ | |
|---|---|--|
| Nominal input frequency | 50/60 Hz | |
| Nominal output voltage | 5.0 V | |
| Nominal input current | 0.3 A | |
| Maximum output current Type-A + Type-C Maximum output current Type-C | 3.0 A shared on A and C output 3.0 A | |
| Power consumption | 15.0 W | |
| Average efficiency in active mode | 80.3 % | |
| Stand-by power consumption | < 0.07 W | |
| Consumption class without load and average level of efficiency: Level VI* | | |
| Protection class | ll - Low voltage | |

*Nota: European Regulation No. 278/2009 of 6 April 2009, Directive 2009/125/EC on eco-design requirements for AC/DC power supplies.

Note : To optimize the charging time of your device, ensure turn it off during the charging phase.

Céliane[™] USB Type-A + USB Type-C charger USB Type-C charger

6. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichlorethylene.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards. Refer to e-catalogue.