


Valena™ Next

Connected wireless control for roller shutters and orientable sun shades

Cat. Nos: 7 418 08/38/68



1. USE


Zone or centralised control for wired roller shutters and orientable sun shades switches.

- Fixes directly on the wall or screws onto a flush-mounting box.
 - Multi-gang versions can be combined with other wiring accessories.
 - Fits on a piece of furniture (movable).
- Can control up to 20 roller shutters switches.

2. RANGE


Description	White	Alu	Black
Connected wireless control for roller shutters and orientable sun shades (OSS). Supplied complete with battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.	7 418 08	7 418 38	7 418 68

3. DIMENSIONS (mm)



A	B	C
83	83	12

4. OPERATION



5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02
 Protection against solid bodies/liquids: IP 20 without plate and rocker plate
 IP 40 for assembled product

■ 5.2 Material characteristics

Plates: - ABS White (RAL 9003) polyglass appearance
 - ABS painted satin appearance for other colors
 Subplate: opalescent white PC
 Mechanism with grid: Fibreglass-reinforced (10%) PC

Halogen-free
 UV-resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)
 Battery life: 8 years for 10 activations a day

ZigBee radio technology

Frequency: 2.4 GHz to 2.4835 GHz
 Power level: < 100 mW

■ 5.4 Climate characteristics

Usage temperature: +5°C to +45°C
 Storage temperature: 0°C to +45°C

6. CARE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

The plates must not be painted.



Take care to recycle the battery appropriately

7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (supplied)

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 418 08/38/68) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com