


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Telephone: (+33) 05 55 06 87 87 - Fax: (+33) 5 55 06 88 88 www.legrand.com

Céliane[™] 4 AX - 6 AX two-way switches

Cat. No(s): 0 670 07/13/15/16




1. USE


Lighting control mechanisms with or without locating elements. Multi mounting in horizontal and vertical. Can be equipped with all Céliane finishes.

2. RANGE

Description	Cat. Nos
Two-way switch with indicator light, without neutral (with white LED) - Lever-type 1 gang	0 670 07
Two-way switch silent - Lever-type Mechanism supplied with rocker (only titanium finish) 1 gang	0 670 13
Two-way switch - Push-type Mechanism supplied with rocker (only titanium finish) ON/OFF mechanism by short press - 1 gang	0 670 15
Two-way switch - Lever-type Mechanism supplied with rocker (only titanium finish) 1 gang	0 670 16

3. DIMENSIONS (mm)





Cat. Nos	А	В	с	D
0 670 07	45	45	42.5	9
0 670 13	45	45	38.5	16.5
0 670 15	45	45	41	5
0 670 16	45	45	38.5	13

4. CONNECTION

Cat. Nos	Type of terminals	Terminal capacity	Stripping length
0 670 07	With screws	2 x 1.5 mm ²	8 mm
0 670 13/16	automatic	2 x 2.5 mm ²	13 mm
0 670 15	With screws	2 x 4 mm ²	11 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK 04 Penetration by solid bodies and liquids: IP 20

5.2 Material characteristics PC

Halogen free

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place. + 650° C / 30 s for other parts made of insulating materials.

5.3 Electrical characteristics

Cat. Nos	Current	Voltage
0 670 07	4 AX max. (60 W min.)	250 V~
0 670 13/15/16	6 AX	250 V~

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 50° C

6. CLEANING

Rocker Cat. No. 0 670 13/16:

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichlorethylene.

Caution: A preliminary test should be carried out if specific cleaning
products are to be used.
·

6. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.