


SUNO™ - SEANO™
Connected Wake up/Sleep wireless control

Cat. No(s): 7 221 77 - 7 222 77 - 7 223 77 - 7 224 77
7 656 37 - 7 657 37 - 7 658 37 - 7 659 37



7 221 77, 7 656 37

1. USE


Used to control wake up/sleep scenes involving lights, roller shutters and connected sockets.

- Fixes directly on the wall or screws onto a flush-mounting box.
- Multi-gang versions can be combined with other wiring accessories.
- Fits on a piece of furniture (movable).

2. RANGE


| Description | Family | White | Ivory | Aluminum | Black | Dark Grey |
|--------------------------------|--------|----------|----------|----------|----------|-----------|
| Wireless remote wake up/ sleep | SUNO | 7 221 77 | 7 222 77 | 7 223 77 | 7 224 77 | - |
| | SEANO | 7 656 37 | - | 7 657 37 | 7 658 37 | 7 659 37 |

3. DIMENSIONS (mm)



| References | A | B | C |
|--------------------|------|------|------|
| 7 221 77, 7 656 37 | 72.9 | 72.9 | 11.5 |

4. OPERATION



5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02
Protection against solid bodies/liquids:
- IP 20 without plate and rocker plate
- IP 40 for assembled product

■ 5.2 Material characteristics

Plate: ABS
Sub-plate: PC
Rocker plate: ABS
Colours: White RAL 9003 - Ivory RAL 1013
Aluminium, Black, Dark Grey
Mechanism casing with support: Fibreglass-reinforced (10 %) PC
Halogen-free
UV resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)
Battery life: 8 years for 10 activations a day
Frequency band: 2.4 to 2.44835 GHz
Power level: < 100 mW

■ 5.4 Climatic characteristics

Usage temperature: + 5° C to + 45° C
Storage temperature: 0° C to + 45° C

6. MAINTENANCE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.
Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, windowcleaning products, pre-impregnated wipes

Caution: Always test before using other special cleaning products.

Do not paint the cover plate.



Take care to recycle the battery appropriately.

7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (Cat. Nos 7 221 77 - 7 222 77 7 223 77 - 7 224 77 - 7 656 37 - 7 657 37 - 7 658 37 - 7 659 37) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue