


Valena™ Life

Wireless colour ambiance switch

Cat. No(s): 7 521 83 - 7 522 83 - 7 523 83 - 7 563 83
 1 993 30/31



1. USE


Wireless switch to control multicolor smart lighting.
 Controls any kind of Zigbee 3.0 certified bulbs and lighting (such as Ledvance, Smart + Zigbee, Philips HUE and many others).
 Can be used as a two-way switch or to control a lighting group.
 • Se fixe directement sur un mur ou se visse sur une boîte d'encastrement.
 • Multi-gang versions can be combined with other wiring accessories.
 • Fits on a piece of furniture (movable).
 Can control up to 20 connected zigbee 3.0 lights.

2. RANGE

Wireless switch for multicolor ambiance - 2 modules
 3 ambiances (I - II - III) to select in Home + Control App.
 Supplied with battery.
 Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings.
 Repositionable self-adhesive fixings (supplied).



White	Ivory	Alu	Black
7 521 83	7 522 83	7 523 83	7 563 83
1 993 30	-	1 993 31	-

3. DIMENSIONS (mm)



A	B	C
75	75	12

4. OPERATION



RESET button used to return to factory settings

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02
 Protection against solid bodies and/or liquids: IP 20
 IP 40 mounted product

■ 5.2 Material characteristics

Mechanism casing with grid: Fibreglass-reinforced (10%) PC
 Plate: ABS
 Sub-plate: PC
 Rocker: ABS
 Halogen-free
 UV-resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)
 Battery life: 8 years for 10 activations a day

Zigbee radio technology

Frequency bands: 2.4 GHz to 2.4835 GHz
 Power level: < 100 mW

■ 5.4 Climate characteristics

Usage temperature: +5°C to + 45°C
 Storage temperature: 0°C to + 45°C

6. CARE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:
Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

Do not paint the plates.



Take care to recycle the battery appropriately.

7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (supplied)

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 521 83 - 7 522 83 - 7 523 83 - 7 563 83 - 1 993 30/31) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com