


Valena™ Life

Connected wireless control for roller shutters and orientable sun shades

Cat. Nos: 7 521 91 - 7 522 91 - 7 523 91



1. USE

Zone or centralised control for wired roller shutters and orientable sun shades switches.

- Fixes directly on the wall or screws onto a flush-mounting box. Multi-gang versions can be combined with other wiring accessories.
- Fits on a piece of furniture (movable).

Can control up to 20 roller shutter switches.

2. RANGE


Connected wireless control for roller shutters and orientable sun shades (OSS). Supplied complete with battery.


Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings.

Repositionable self-adhesive fixings supplied.


White	lvory	Aluminium	Mat Black
7 521 91	7 522 91	7 523 91	7 563 91


3. DIMENSIONS (mm)





4. OPERATION





RESET button used to return to factory settings

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies/liquids:

- IP 20 without plate and rocker plate
- IP 40 for assembled product

■ 5.2 Material characteristics

Plate: ABS

Sub-plate: PC

Rocker plate: ABS

Mechanism with grid: Fibreglass-reinforced (10%) PC

Halogen-free

UV-resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

ZigBee radio technology

Frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

■ 5.4 Climate characteristics

Usage temperature: $+ 5^{\circ}\text{C}$ to $+ 45^{\circ}\text{C}$ Storage temperature: 0°C to $+ 45^{\circ}\text{C}$

Valena™ Life **Connected wireless control for roller shutters** and orientable sun shades

Cat. Nos: 7 521 91 - 7 522 91 - 7 523 91

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene. Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, windowcleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

The plates must not be painted.



Take care to recycle the battery appropriately

7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 521 91 - 7 522 91 - 7 523 91) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com

2/2