


1. USE

Charger with side connection via bistable automatic terminals. For recharging portable devices such as phones, smartphones, tablets, MP3 or MP4 players, loudspeakers, watches, game consoles, powerbanks Supplied without a cord.

2. RANGE

5.0 V 3.0 A USB charger	White	Alu	Matt Black
1 Mosaic Link USB Type-A + 1 Mosaic Link USB Type-C (1 Type-A output - 1 Type-C output) Can be combined with other Mosaic Link socket outlets using connection accessory Cat. No. 0 771 00L.	0 775 70L	0 792 93L	0 791 93L

3. DIMENSIONS (mm)



4. CONNECTION

Type of terminals: automatic with side connection Number of terminals: 2 inputs - 2 outputs Terminal capacity: 2 x 2.5 mm² Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Impact tests: IK 04 Penetration by solid bodies/liquid: IP 40

■ 5.2 Material characteristics

Base: PC

Cover-plate: ABS White RAL 9003 Painted glittery varnished aluminium Painted satin-finish matt black RAL 9017

Halogen-free UV-resistant

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

■ 5.3 Climate characteristics

Storage temperature: - 20° C to + 70° C Usage temperature: + 5° C to + 45° C

■ 5.4 Electrical characteristics

All values listed below are measured at an ambient temperature of $+ 25^{\circ}$ and after 15 minutes of operation.

Nominal input voltage	100-240 V~	
Nominal input frequency	50/60 Hz	
Power	15.0 W	
Maximum input current	0.5 A	
Maximum power consumption in standby	0.075 W	
Power average efficiency	80.3%	
Nominal output voltage	5.0 V==	
Maximum output current Type-A + Type-C	3.0 A shared over outputs A and C	
No-load power consumption class and average efficiency level: Level VI*		
Protection class	ll - Low voltage	
	·	

*NB: EU/2019/1782 October 2019, Directive 2009/125/EC on eco-design requirements for AC/DC power supplies.

Note: To optimize the charging time of your device, make sure it is turned off during the charging phase.

6. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichlorethylene.

Caution: Always test before using other special cleaning products.

7. ACCESSORIES

0 771 00L: Mosaic Link connection accessory, used to link 2 Mosaic Link socket outlets or 2 socket blocks quickly and easily.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. Refer to e-catalogue.