


Valena™ Next Wireless 4 scenes control

Cat. No(s): 7 418 02/32/62



1. USE

Allows control of all connected wired controls (lights, appliances, roller shutters).


Requires the prior installation of a starter pack for connected installation or a Control modul.

Fixes directly on the wall or screws onto a flush-mounting box. Multigang versions can be combined with other wiring accessories. Fits on a furniture (movable).

2. RANGE


Description	Blanc	Alu	Noir
Wireless control connected, 4 configurable scenarios. Supplied complete with battery. With LED indicator (configuration) and RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.	7 418 02	7 418 32	7 418 62


3. DIMENSIONS



Α	В	С
83	83	12

4. OPERATION





5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02

Protection against solid bodies/liquids: IP 20 without plate and rocker plate IP 40 for assembled product

■ 5.2 Material characteristics

Plates: ABS White (RAL 9003) polyglass appearance ABS painted satin appearance for other colors

Subplate: opalescent white PC

Mechanism with grid: Fibreglass-reinforced (10%) PC

Halogen-free

UV-resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

Frequency band: 2.4 to 2.44835 GHz

Power level: < 100 mW

■ 5.4 Climate characteristics

Usage temperature: $+ 5^{\circ}\text{C}$ to $+ 45^{\circ}\text{C}$ Storage temperature: 0°C to $+ 45^{\circ}\text{C}$

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

Do not paint the cover plate.



Take care to recycle the battery appropriately

7. ACCESSORIES

0 648 71: Repositionable adhesives for wireless control (supplied)

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 418 02/32/62) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: **www.legrandoc.com**

Compliant with installation and manufacturing standards. See e.catalogue.