



Niloe™ STEP IP44 Socket outlets


Cat. Nos: 3 982 47 - 8 631 23B - 8 631 35B - 8 631 36B - 8 633 35B
- 8 633 36B - 8 634 35B - 8 634 36B - 8 635 23B - 8 635 35B -
8 635 36B - 8 641 35 - 8 641 39B



3 982 47, 8 631 23B/39B,
8 641 23B/39B, 8 635 23B



8 63X 35B



8 63X 36B


1. USE

2 P+E sealed socket outlets with shutters.
Supplied with cover plates and support frames.
To be fitted with single module or multi-module plates.
Screws fixing.

2. RANGE

Designation	White	Aluminium	Medium Grey	Black
IP44 2P+E SOCKET FRENCH STANDARD AUTO TERMINALS	8 631 35B	8 633 35B	8 634 35B	8 635 35B
IP44 2P+E SOCKET FRENCH STANDARD AUTO TERMINALS SHUTTERED	8 631 36B	8 633 36B	8 634 36B	8 635 36B
IP44 2P+E SOCKET GERMAN STANDARD AUTO TERMINALS SHUTTERED	3 982 47, 8 641 35 8 631 23B, 8 641 39B	-	-	8 635 23B

3. DIMENSIONS (mm)



References	A	B	C	D
8 63X 35B	92	86	29.4	15.8
8 63X 36B	92	86	28.8	16.3
3 982 47, 8 641 35/39B, 8 631 23, 8 635 23B	92	86	29.4	18.8

4. CONNECTION

Type of terminals: automatics
Terminals capacity: 2 x 2.5 mm²
Compatible flexible or rigid cables.
Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 44
Protection against impacts: IK 04

■ 5.2 Material characteristics

Mat appearance

Material: - Cover plates: PC
- UV resistant

Material of the support: - PC grey RAL 7016
- Halogen free

Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

Voltage: 250 V~
Current: 16 A
Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage temperature: -10°C to +70°C
Usage temperature: -5°C to +40°C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the cleaning agents: Hexane, Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning substances, Pre-impregnated wipes.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (Cat. Nos: 3 982 47 - 8 631 23B - 8 631 35B - 8 631 36B - 8 633 35B - 8 633 36B - 8 634 35B - 8 634 36B - 8 635 23B - 8 635 35B - 8 635 36B - 8 641 35 - 8 641 39B) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue