



# Céliane™

## Decorative plates with graphik finish

Cat. No(s): CP0601/02/03/04/06/07/08/11/21/22/23/24  
 CP0701/02/03/04/06/07/08/11/21/22/23/24



CP0601



CP0703

### 1. USE

Faceplates for 1-gang to 4-gang wiring accessories.  
 Horizontal or vertical mounting.  
 Indoor use only.

### 2. RANGE

#### 1-gang plates

	Relieved white	CP0601	CP0621
	Meteor black	CP0701	CP0721

#### 2-gang plates - Center distance 71 mm

	Relieved white	CP0602	CP0622
	Meteor black	CP0702	CP0722

#### 3-gang plates - Center distance 71 mm

	Relieved white	CP0603	CP0623
	Meteor black	CP0703	CP0723

#### 4-gang plates - Center distance 71 mm

	Relieved white	CP0604	CP0624
	Meteor black	CP0704	CP0724

#### 2-gang plates - Center distance 57 mm

	Relieved white	CP0606	
	Meteor black	CP0706	

#### 3-gang plates - Center distance 57 mm

	Relieved white	CP0607	
	Meteor black	CP0707	

### 2. RANGE (continued)


#### Extended 2-station plates (4/5 modules)

	Relieved white	CP0608	
	Meteor black	CP0708	

#### Extended 3-station plates (6/8 modules)

	Relieved white	CP0611	
	Meteor black	CP0711	

### 3. DIMENSIONS (mm)



References	A	B	C
CP0601/621/701/721	82	90	9
CP0602/622/702/722	82	161	9
CP0603/623/703/723	82	232	9
CP0604/624/704/724	82	303	9
CP0606/706	82	147	9
CP0607/707	82	204	9
CP0608/708	82	161	9
CP0611/711	82	232	9

#### 4. TECHNICAL CHARACTERISTICS

##### ■ 4.1 Mechanical characteristics

Protection against impacts: IK 04

##### ■ 4.2 Material characteristics

Plate: Matte black painted PC with hatch graphics

RAL 9003 white PC with raised curved graphics

Underplate: ABS

Halogen-free

UV-resistant

Self-extinguishing: 650°C/30 s

##### ■ 4.3 Climate characteristics

Storage temperature: - 10°C to + 70°C

Usage temperature: - 5°C to + 50°C

#### 5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following products:

Hexane, methylated spirit, soapy water, window-cleaning products.

**Caution:** Always test before using other special cleaning products

No paint should be applied to the plates.

#### 6. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.