


Niloé™ Next
Socket outlets - German Standard

Cat. No(s): NNP3199BL/MG/WH, NNP3120BL/MG/WH,
 NNP3130BL/WH




1. USE

Socket outlets with shutters.
 Mechanisms supplied with protection cover.
 To be equipped with plates one or several gangs.
 Flush-mounting.
 Screw or claw fixing.

2. RANGE

Description	White	Medium Grey	Black
2x2 P+E socket automatic terminal	NNP3130WH	-	NNP3130BL
2 P+E socket automatic terminal	NNP3120WH	NNP3120MG	NNP3120BL
2 P socket screw terminal	NNP3199WH	NNP3199MG	NNP3199BL

3. DIMENSIONS (mm)



References	A	B	C	D
NNP3199..	75.8	75.8	30.82	10
NNP3120..	75.8	75.8	43.8	13

References	A	B	C	D
NNP3130..	104	86	53,8	22,3

4. CONNECTION

Terminal capacity: 2 x 2.5 mm²

Type of terminals: automatic

Screw terminal: NNP3199..

Stripping length:

13mm NNP3130..

12 mm NNP3120..

9 mm NNP3199..

Flexible or rigid cables compatible

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20

Protection against impact: IK 04

■ 5.2 Material characteristics

Mat appearance

Mechanism housing: PC

Cover plate: PC

UV-resistant

Claws: steel

Support: PC

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place

650°C/30 s for other insulating components

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 16 A

Frequency: 50/60 Hz

■ 5.4 Climate characteristics

Storage temperature: - 10° C to +70° C

Usage temperature: - 5° C to + 40° C

6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products:

Hexane, methylated spirit, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products.

Caution: Always test before using other special cleaning products

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (Cat. Nos NNP3120BL/MG/WH - NNP3130BL/WH - NNP31990BL/MG/WH) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue